

Tehničke karakteristike proizvoda

Karakteristike

XVC6M2

60mm svetlosna kolona CN na dršci
100-240VAC



Osnovne informacije

Grupa proizvoda	Harmony XVC6
Tip proizvoda ili komponente	Kompletno ožičena monolitna svetleća kolona
Tip baze svetleće kolone ili semafora	2 svetleće jedinice
Zvučni signal	Bez
Prečnik za montiranje	60 mm
Ime komponente	XVC
Svetlosni izvor	LED trajna crvena LED trajna narandžasta
[us] nazivni napon	100...240 V
Tip kola napajanja	AC

Dopunske informacije

Materijal	Polikarbonat: svetleća jedinica ABS (akrilonitril-butadien-stiren): bazi PBT + ABS (UL94-V0): gornji poklopac
Montaža proizvoda	Na cevnom nosaču, 22 mm
Poprečni presek kabla	0,33 Mm ² 0,83 mm ²
Awg mera (američki standard za prečnik žice)	AWG 18 AWG 22
Dužina kabla	450 Mm 550 mm
Označavanje	CE
[uimp] nazivni napon impulsa	4 kV
Struja potrošnje	50 mA
Masa proizvoda	1,02 kg
Visina	639,8 mm

Okruženje

Standardi	IEC 60947-1 IEC 60947-5-1
Sertifikacija proizvoda	UL
Tretman zaštite	TC
Temperatura okoline za skladištenje	-35...70 °C
Temperatura okoline za rad uređaja	-10...50 °C
Klasa zaštite protiv električnog udara	Klasa I u skladu sa IEC 61140
Ip stepen zaštite	IP23 instalaciji na vertikalnu površinu u skladu sa IEC 60529

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,7 cm
Package 1 Width	9,0 cm
Package 1 Length	77,7 cm
Package 1 Weight	1,189 kg

Unit Type of Package 2	S06
Number of Units in Package 2	10
Package 2 Height	73,5 cm
Package 2 Width	60,0 cm
Package 2 Length	80,0 cm
Package 2 Weight	26,89 kg

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b1 dimension.



No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	599.8	23.61
2 stages	639.8	25.19
3 stages	679.8	26.76
4 stages	719.8	28.34
5 stages	759.8	29.91

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting

