

Tehničke karakteristike proizvoda

Karakteristike

XVC6M25SK

60mm svetlosna kolona CN montaža na bazu -
zujalica, trepćuća 100-240VAC



Osnovne informacije

Grupa proizvoda	Harmony XVC6
Tip proizvoda ili komponente	Kompletno ožičena monolitna svetleća kolona
Tip baze svetleće kolone ili semafora	2 svetleće jedinice
Zvučni signal	Zujalica
Prečnik za montiranje	60 mm
Ime komponente	XVC
Svetlosni izvor	LED trajna ili treperenje crvena LED trajna ili treperenje narandžasta
[us] nazivni napon	100...240 V
Tip kola napajanja	AC
Nivo buke	70...85 dB (stalni ili isprekidani ton) pri 1 m

Dopunske informacije

Materijal	Polikarbonat: svetleća jedinica ABS (akrilonitril-butadien-stiren): bazi PBT + ABS (UL94-V0): gornji poklopac
Montaža proizvoda	Na bazi
Poprečni presek kablova	0,33 Mm ² 0,83 mm ²
Awg mera (američki standard za prečnik žice)	AWG 18 AWG 22
Dužina kablova	850 Mm 750 mm
Označavanje	CE
[uimp] nazivni napon impulsa	4 kV
Struja potrošnje	75 mA
Frekvencija osnovnog harmonika	2,23 kHz
Frekvencija treptanja	1 Hz
Masa proizvoda	0,55 kg
Visina	272 mm

Okruženje

Standardi	EN/IEC 60947-5-1 EN/IEC 60947-1
Sertifikacija proizvoda	UL
Tretman zaštite	TC
Temperatura okoline za skladištenje	-35...70 °C
Temperatura okoline za rad uređaja	-10...50 °C
Klasa zaštite protiv električnog udara	Klasa I u skladu sa EN/IEC 61140
Ip stepen zaštite	IP54 instalaciji na ravnu površinu u skladu sa EN/IEC 60529

Održivost ponude

EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



No. of illuminated units	b (mm)	b (in.)
1 stage	232	9.13
2 stages	272	10.71
3 stages	312	12.28
4 stages	352	13.86
5 stages	392	15.43

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

