

Tehničke karakteristike proizvoda

Karakteristike

XVMB2RAGBSWSB

svetlosna kolona sa zujalicom + 4 svetleće
jedinice - Ø 45 mm - 24 V AC/DC



Osnovne informacije

Grupa proizvoda	Harmony XVM
Tip proizvoda ili komponente	Sastavljena i prefabrikovana svetleća kolona
Tip baze svetleće kolone ili semafora	4 svetleće jedinice
Ime komponente	XVM
Svetlosni izvor	Zelena izrazito sjajan LED sa BA 15d bazi trajna signalizacijom Narandžasta izrazito sjajan LED sa BA 15d bazi trajna signalizacijom Crvena izrazito sjajan LED sa BA 15d bazi trajna signalizacijom Plava izrazito sjajan LED sa BA 15d bazi trajna signalizacijom
Boja svetlosnog bloka	Crvena/narandžasta/zelena/plava
[us] nazivni napon napajanja	24 V AC/DC
Tip baze svetleće kolone	Baza sa integrisanom zujalicom
Način montiranja	Horizontalna

Dopunske informacije

Sastav seta	Poklopac Plastična pločica za montažu Baza
Prečnik za montiranje	45 mm
Povezivanje - priključci	Žičani završeci, 1 x 0.325 mm ² (AWG 22)
Označavanje	CE
Držač za montažu	baza
Zaštita od preopterećenja i kratkog spoja	0,2 A
[ui] nazivni napon izolacije	250 V u skladu sa IEC 60947-1
Nazivno ograničenje napona	0.85...1.1 Un u skladu sa IEC 60947-5-1
Potrošnja struje	18 mA na bazi 20 mA na jedinici za snažan bljesak
[uimp] nazivni podnosivi impulsni napon	4 kV u skladu sa IEC 60947-1
Frekvencija treperenja	0,8 Hz
Frekvencija osnovnog harmonika	4 kHz
Masa proizvoda	0,3 kg

Okruženje

Ip stepen zaštite	IP54 horizontalnoj poziciji u skladu sa IEC 60529
Sertifikacija proizvoda	CCC
Standardi	EN/IEC 60947-5-1 EN/IEC 60947-1
Temperatura okoline za skladištenje	-25...70 °C
Temperatura okoline za rad uređaja	-10...50 °C

Kategorija prenapona	Klasa II u skladu sa IEC 60947-1 Klasa II u skladu sa IEC 60947-5-1 Klasa II u skladu sa IEC 61140
Tretman zaštite	TC
Nivo buke	0...80 dB pri 1 m

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.


Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Pre-Assembled and Pre-Cabled Tower Light with Fixing Base for Mounting on Horizontal Support (Plastic Fixing Plate)

Dimensions

Below drawing shows a tower light with 3 illuminated stages. Select the number of stages according to the product characteristics in order to get b dimension.



(1) Base unit with or without buzzer.

Number of illuminated units	b in mm	b in in.
1 unit	150	5.90
2 units	215	8.46
3 units	280	11.02
4 units	345	13.58

Pre-Assembled and Pre-Cabled Tower Light

Wire Colors

4th illuminated unit: yellow wire

3rd illuminated unit: green wire

2nd illuminated unit: white wire

1st illuminated unit: blue wire


Common: black wire

Buzzer (if integrated in base unit): grey wire

Base Unit with Integral Buzzer

Adjustment of Audible Signal

View from above:



- (1) Volume adjustment potentiometer: 0 to 85 dB. Use either a cross headed or flat tipped screwdriver.
- (2) 2-position selector for type of audible signal: continuous tone or intermittent tone