

A9F95125

Miniature circuit breaker (MCB), Acti9 iC60L,
1P, 25A, K curve, 15000A (IEC/EN 60898-1),
25kA (IEC/EN 60947-2)

Main

Device application	Distribution
Range	Acti9
Product name	Acti9 iC60
Product or component type	Miniature circuit-breaker
Device short name	iC60L
Poles description	1P
Number of protected poles	1
[In] rated current	25 A
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	K
Breaking capacity	15000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1 70 KA Icu at 12...60 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 KA Icu at 72 V DC conforming to EN/IEC 60947-2 25 KA Icu at 12...48 V DC conforming to EN/IEC 60947-2 25 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2
Utilisation category	Category A conforming to EN 60947-2 Category A conforming to IEC 60947-2
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Standards	EN 60947-2 IEC 60947-2

Complementary

Network frequency	50/60 Hz
Magnetic tripping limit	12 x In +/- 20 %
[Ics] rated service breaking capacity	12.5 KA 50 % conforming to EN 60947-2 - 220...240 V AC 50/60 Hz 12.5 KA 50 % conforming to IEC 60947-2 - 220...240 V AC 50/60 Hz 35 KA 50 % conforming to EN 60947-2 - 12...60 V AC 50/60 Hz 35 KA 50 % conforming to IEC 60947-2 - 12...60 V AC 50/60 Hz 25 KA 50 % conforming to EN 60947-2 - 100...133 V AC 50/60 Hz 25 KA 50 % conforming to IEC 60947-2 - 100...133 V AC 50/60 Hz 20 KA 100 % conforming to EN 60947-2 - 72 V DC 20 KA 100 % conforming to IEC 60947-2 - 72 V DC 25 KA 100 % conforming to EN 60947-2 - 12...60 V DC 25 kA 100 % conforming to IEC 60947-2 - 12...60 V DC
Limitation class	3 conforming to EN 60898-1 3 conforming to IEC 60898-1
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN 60947-2 500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 KV conforming to EN 60947-2 6 kV conforming to IEC 60947-2
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Fixed

Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	78.5 mm
Net weight	0.215 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Single terminal (top or bottom) 1...25 mm ² rigid Single terminal (top or bottom) 1...16 mm ² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Without



Environment

IP degree of protection	IP20 conforming to IEC 60529 IP20 conforming to EN 60529
Pollution degree	3 conforming to EN 60947-2 3 conforming to IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	0...2000 m
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.700 cm
Package 1 Width	7.200 cm
Package 1 Length	9.300 cm
Package 1 Weight	116.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.300 cm
Package 2 Width	10.000 cm
Package 2 Length	22.400 cm
Package 2 Weight	1.448 kg
Unit Type of Package 3	S02
Number of Units in Package 3	48
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.687 kg

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
SCIP Number	26ff71d1-98cf-4280-8725-455b9a6b2fb9
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	17

Contractual warranty

Warranty	18 months
----------	-----------