

Tehničke karakteristike proizvoda Karakteristike

GZ1AN11

Easypact TVS - pomoćni kontakt montaža na
levoj strani - NO+NC



Osnovne informacije

Grupa proizvoda	Easy TeSys Power
Grupa proizvoda	Easy TeSys
Tip proizvoda ili komponente	Pomoćni kontakti blok
Kratko ime uređaja	GZ1AN
Povezivanje - priključci	Vijčani priključni blokovi 1 kabl(ovi) 1... 2,5 mm ² jednožični Vijčani priključni blokovi 2 kabl(ovi) 1... 2,5 mm ² jednožični Vijčani priključni blokovi 1 kabl(ovi) 0,75... 2,5 mm ² fleksibilni bez kablovskog završetka Vijčani priključni blokovi 2 kabl(ovi) 0,75... 2,5 mm ² fleksibilni bez kablovskog završetka Vijčani priključni blokovi 2 kabl(ovi) 0,75... 1,5 mm ² fleksibilni sa Vijčani priključni blokovi 1 kabl(ovi) 0,75... 1,5 mm ² fleksibilni sa

Dopunske informacije

Kompatibilnost grupe proizvoda	Easypact EasyPact TVS GZ1E prekidač
Lokacija za montiranje	Leva strana
Operacije pomoćnih kontakata	Trenutno 1 NO + 1 NC
Raspored kontakata	1 NO + 1 NC
[ui] nazivni napon izolacije	690 V u skladu sa IEC 60947-1
[ue] nazivni radni napon	48...690 V AC 24...240 V DC
[ith] dozvoljena termička struja u vazduhu	6 A
Tip zaštite	GG osigurač 10 A
Mehanička trajnost	100000 ciklusa
Minimalna struja preklapanja	5 mA
Minimalni napon preklapanja	17 V
Nazivna snaga u va	300 VA pri 48 V AC-15 - električna trajnost: 70000 ciklusa 400 VA pri 690 V AC-15 - električna trajnost: 70000 ciklusa 500 VA pri 110...127 V AC-15 - električna trajnost: 70000 ciklusa 500 VA pri 500 V AC-15 - električna trajnost: 70000 ciklusa 650 VA pri 440 V AC-15 - električna trajnost: 70000 ciklusa 720 VA pri 230...240 V AC-15 - električna trajnost: 70000 ciklusa 850 VA pri 380...415 V AC-15 - električna trajnost: 70000 ciklusa
Nazivna snaga u w	120 W pri 240 V DC-13 - električna trajnost: 70000 ciklusa 140 W pri 110 V DC-13 - električna trajnost: 70000 ciklusa 140 W pri 24 V DC-13 - električna trajnost: 70000 ciklusa 180 W pri 60 V DC-13 - električna trajnost: 70000 ciklusa 240 W pri 48 V DC-13 - električna trajnost: 70000 ciklusa
Visina	89 mm
Širina	9,3 mm
Dubina	66 mm
Masa proizvoda	0,05 kg

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,500 cm
Package 1 Width	6,500 cm
Package 1 Length	8,500 cm
Package 1 Weight	43,300 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	9,500 cm
Package 2 Length	15,000 cm
Package 2 Weight	488,000 g
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Height	15,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	3,156 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	 Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.