



Tehničke karakteristike proizvoda Karakteristike

LC1D258E7 TeSys D kontaktor - 4P(2 NO + 2 NC) - AC-1 - ≤ 440 V 40 A - 48 V AC kalem



Osnovne informacije

Grupa proizvoda	TeSys Deca
Tip proizvoda ili komponente	Kontaktör
Kratko ime uređaja	LC1D
Primena kontaktora	Rezistivno opterećenje
Kategorija upotrebe	AC-1 AC-3 AC-3e AC-4
Broj polova	4P
[ue] nazivni napon	Kolo napajanja: ≤ 690 V AC 25...400 Hz
[ie] nazivna struja	40 A (at <60 °C) at ≤ 440 V AC AC-1 for kolo napajanja
[Uc] control circuit voltage	48 V AC 50/60 Hz

Dopunske informacije

Kompatibilnost	LC1D
Sastav kontakta strujnog pola	2 NO + 2 NC
Prednja korica	Sa
[ith] dozvoljena termička struja u vazduhu	10 A (at 60 °C) for signalno kolo 40 A (at 60 °C) for kolo napajanja
Irms nazivna moć uključenja	140 A AC for signalno kolo conforming to IEC 60947-5-1 250 A DC for signalno kolo conforming to IEC 60947-5-1 450 A at 440 V for kolo napajanja conforming to IEC 60947
Nazivna prekidna moć	450 A at 440 V for kolo napajanja conforming to IEC 60947
[icw] kratkotrajna podnosiva struja kratkog spoja	240 A 40 °C - 10 s for kolo napajanja 380 A 40 °C - 1 s for kolo napajanja 50 A 40 °C - 10 min for kolo napajanja 120 A 40 °C - 1 min for kolo napajanja 100 A - 1 s for signalno kolo 120 A - 500 ms for signalno kolo 140 A - 100 ms for signalno kolo
Pripadajući osigurač	10 A gG for signalno kolo conforming to IEC 60947-5-1 63 A gG at ≤ 690 V coordination tip 1 for kolo napajanja 40 A gG at ≤ 690 V coordination tip 2 for kolo napajanja
Prosečna impedansa	2 mΩ - Ith 40 A 50 Hz for kolo napajanja
Snaga disipacije po polu	3,2 W AC-1
[ui] nazivni napon izolacije	Kolo napajanja: 690 V u skladu sa IEC 60947-4-1 Kolo napajanja: 600 V CSA sertifikovano Kolo napajanja: 600 V UL sertifikovano Signalno kolo: 690 V u skladu sa IEC 60947-1 Signalno kolo: 600 V CSA sertifikovano Signalno kolo: 600 V UL sertifikovano
Kategorija prenapona	III
Stepen zaprljanosti	3
[uimp] nazivni podnosivi impulsni napon	6 kV u skladu sa IEC 60947
Nivo sigurnosne pouzdanosti	B10d = 1369863 ciklusa kontaktor sa nazivnim opterećenjem u skladu sa EN/ISO 13849-1 B10d = 20000000 ciklusa kontaktor sa mehaničkim opterećenjem u skladu sa EN/ISO 13849-1

Mehanička trajnost	15 miliona ciklusa
Električna trajnost	1,4 miliona ciklusa 40 A AC-1 pri $U_e \leq 440$ V
Tip upravljačkog kola	AC pri 50/60 Hz
Tehnologija kalema	Bez ugrađenog prigušivača
Ograničenje napona upravljačkog kola	0.3...0.6 U_c -40...60 °C propad napona AC 50/60 Hz 0.8...1.1 U_c -40...60 °C u radu AC 50 Hz 0.85...1.1 U_c -40...60 °C u radu AC 60 Hz
Udarne snaga u va	70 VA 60 Hz $\cos \phi$ 0,75 (at 20 °C) 70 VA 50 Hz $\cos \phi$ 0,75 (at 20 °C)
Snaga držanja u va	7,5 VA 60 Hz $\cos \phi$ 0,3 (at 20 °C) 7 VA 50 Hz $\cos \phi$ 0,3 (at 20 °C)
Disipacija toplote	2...3 W at 50/60 Hz
Vreme uključenja/isključenja	12...22 ms zatvaranje 4...19 ms otvaranje
Maksimalni radni ciklus	3600 ciklusa/h pri <60 °C
Maksimalni radni ciklus	3600 ciklusa/h at 60 °C
Povezivanje - priključci	Upravljačko kolo: vijčani priključni blokovi 1 1...4 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 1...4 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 1 1...4 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Upravljačko kolo: vijčani priključni blokovi 2 1...2,5 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Upravljačko kolo: vijčani priključni blokovi 1 1...4 mm ² - cable stiffness: jednožični bez kablovskog završetka Upravljačko kolo: vijčani priključni blokovi 2 1...4 mm ² - cable stiffness: jednožični bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 1 2,5...10 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 2 2,5...10 mm ² - cable stiffness: fleksibilni bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 1 2,5...10 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Kolo napajanja: vijčani priključni blokovi 2 2,5...10 mm ² - cable stiffness: fleksibilni sa kablovskim završetkom Kolo napajanja: vijčani priključni blokovi 1 2,5...16 mm ² - cable stiffness: jednožični bez kablovskog završetka Kolo napajanja: vijčani priključni blokovi 2 2,5...16 mm ² - cable stiffness: jednožični bez kablovskog završetka
Moment pritezanja	Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi - sa odvijačem matica Ø 6 mm Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi - sa odvijačem Philips No 2 Upravljačko kolo: 1,7 N.m - na vijčani priključni blokovi - sa odvijačem pozidiv broj 2 Kolo napajanja: 1,8 N.m - na vijčani priključni blokovi - sa odvijačem matica Ø 6 mm Kolo napajanja: 1,8 N.m - na vijčani priključni blokovi - sa odvijačem Philips No 2 Kolo napajanja: 1,8 N.m - na vijčani priključni blokovi - sa odvijačem pozidiv broj 2
Sastav pomoćnog kontakta	1 NO + 1 NC
Tip pomoćnog kontakta	Tip mehanički povezani 1 NO + 1 NC u skladu sa IEC 60947-5-1 Tip preslikani kontakt 1 NC u skladu sa IEC 60947-4-1
Frekvencija signalnog kola	25...400 Hz
Minimalni napon preklapanja	17 V for signalno kolo
Minimalna struja preklapanja	5 mA for signalno kolo
Otpornost izolacije	> 10 MOhm for signalno kolo
Vreme nepreklapanja	1,5 Milisekundi pri isključenju između NC i NO kontakta 1,5 milisekundi pri zatvaranju između NC i NO kontakta
Nosači za montažu	Šina Ploča




Okruženje

Standardi	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 60947-4-1 IEC 60335-1:Clause 30.2 IEC 60335-2-40:Annex JJ UL 60335-2-40:Annex JJ CSA C22.2 No 60947-4-1
Sertifikacija proizvoda	UL[RETURN]CCC[RETURN]CSA[RETURN]Marine[RETURN]UKCA[RETURN]EAC[RETURN] Scheme
Ip stepen zaštite	IP20 prednja strana u skladu sa IEC 60529
Zaštitni tretman	TH u skladu sa IEC 60068-2-30
Klimatska izdržljivost	U skladu sa IACS E10 izlaganje toploj i vlažnoj sredini U skladu sa IEC 60947-1 Annex Q category D izlaganje toploj i vlažnoj sredini
Dopustiva temperatura u okolini uređaja	-40...60 °C 60...70 °C sa promenom karakteristika
Nadmorska visina za rad uređaja	0...3000 m
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Otpornost na plamen	V1 u skladu sa UL 94
Mehanička robusnost	Vibracije kontaktor nije u radu (2 Gn, 5...300 Hz) Vibracije na kontaktor u radu (4 Gn, 5...300 Hz) Udara na kontaktor u radu (15 Gn za 11 ms) Udara kontaktor nije u radu (8 Gn za 11 ms)
Visina	91 mm
Širina	45 mm
Dubina	99 mm
Masa proizvoda	0,425 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,800 cm
Package 1 Width	9,500 cm
Package 1 Length	12,000 cm
Package 1 Weight	473,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	8,047 kg
Unit Type of Package 3	P06
Number of Units in Package 3	256
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	136,752 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh free of SVHC	Yes
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
RoHS exemption information	 Yes

RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------