



Tehničke karakteristike proizvoda Karakteristike

LP1K0610BD TeSys K kontaktor - 3P(3 NO) - AC-3 - <= 440 V 6 A - 24 V DC kalem



Osnovne informacije

Grupa proizvoda	TeSys
Tip proizvoda ili komponente	Kontaktör
Kratko ime uređaja	LP1K
Primena kontaktora	Upravljanje motorom

Dopunske informacije

Kategorija upotrebe	AC-3 AC-3e AC-4
Broj polova	3P
Sastav kontakta strujnog pola	3 NO
[ue] nazivni napon	Kolo napajanja: <= 690 V AC <= 400 Hz Signalno kolo: <= 690 V AC <= 400 Hz
[ie] nazivna struja	6 A (at <60 °C) at <= 440 V AC AC-3 for kolo napajanja 6 A (at <60 °C) at <= 440 V AC AC-3e for kolo napajanja
Tip upravljačkog kola	DC standardno
Napon upravljačkog kola	24 V DC
Snaga motora kw	1,5 KW pri 220...230 V AC 50/60 Hz AC-3 2,2 KW pri 380...415 V AC 50/60 Hz AC-3 3 KW pri 440/690 V AC 50/60 Hz AC-3 1,5 KW pri 220...230 V AC 50/60 Hz AC-3e 2,2 KW pri 380...415 V AC 50/60 Hz AC-3e 3 KW pri 440/690 V AC 50/60 Hz AC-3e 1,5 KW pri 220...230 V AC 50/60 Hz AC-4 2,2 KW pri 380...415 V AC 50/60 Hz AC-4 3 KW pri 440/690 V AC 50/60 Hz AC-4
Sastav pomoćnog kontakta	1 NO
[uimp] nazivni podnosivi impulsni napon	8 kV
Kategorija prenapona	III
[ith] dozvoljena termička struja u vazduhu	20 A (at 60 °C) for kolo napajanja 10 A (at 50 °C) for signalno kolo
Irms nazivna moć uključenja	110 A AC for kolo napajanja conforming to IEC 60947 110 A AC for signalno kolo conforming to IEC 60947
Nazivna prekidna moć	110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947

[icw] kratkotrajna podnosiva struja kratkog spoja	90 A 50 °C - 1 s for kolo napajanja 85 A 50 °C - 5 s for kolo napajanja 80 A 50 °C - 10 s for kolo napajanja 60 A 50 °C - 30 s for kolo napajanja 45 A 50 °C - 1 min for kolo napajanja 40 A 50 °C - 3 min for kolo napajanja 20 A 50 °C - >= 15 min for kolo napajanja 80 A - 1 s for signalno kolo 90 A - 500 ms for signalno kolo 110 A - 100 ms for signalno kolo
Pripadajući osigurač	25 A gG at <= 440 V for kolo napajanja 25 A aM for kolo napajanja 10 A gG for signalno kolo conforming to IEC 60947 10 A gG for signalno kolo conforming to VDE 0660
Prosečna impedansa	3 mΩ - lth 20 A 50 Hz for kolo napajanja
[uij] nazivni napon izolacije	Kolo napajanja: 600 V u skladu sa UL 508 Kolo napajanja: 690 V u skladu sa IEC 60947-4-1 Signalno kolo: 690 V u skladu sa IEC 60947-4-1 Signalno kolo: 690 V u skladu sa IEC 60947-5-1 Signalno kolo: 600 V u skladu sa UL 508 Kolo napajanja: 600 V u skladu sa CSA C22.2 No 14 Signalno kolo: 600 V u skladu sa CSA C22.2 No 14
Otpornost izolacije	> 10 MOhm for signalno kolo
Udarna snaga u W	3 W 20 °C)
Snaga držanja u w	3 W pri 20 °C
Disipacija toplote	1,3 W
Ograničenje napona upravljačkog kola	U radu: 0.8...1.15 U _c (at <50 °C) Propad napona: >= 0.10 U _c (at <50 °C)
Povezivanje - priključci	Vijčani priključni blokovi 1 kabl(ovi) 1,5...4 mm ² jednožični Vijčani priključni blokovi 1 kabl(ovi) 0,75...4 mm ² fleksibilni bez kablovskog završetka Vijčani priključni blokovi 1 kabl(ovi) 0,34...2,5 mm ² fleksibilni sa Vijčani priključni blokovi 2 kabl(ovi) 1,5...4 mm ² jednožični Vijčani priključni blokovi 2 kabl(ovi) 0,75...4 mm ² fleksibilni bez kablovskog završetka Vijčani priključni blokovi 2 kabl(ovi) 0,34...1,5 mm ² fleksibilni sa Kolo napajanja: vijčani priključni blokovi 2 kabl(ovi) 1,5 mm ² fleksibilni sa
Maksimalni radni ciklus	3600 ciklusa/h
Tip pomoćnog kontakta	Tip trenutno 1 NO
Minimalna struja preklapanja	5 mA for signalno kolo
Minimalni napon preklapanja	17 V for signalno kolo
Nosači za montažu	Šina Ploča
Moment pritezanja	0,8...1,3 N.M - na vijčani priključni blokovi Philips No 2 0,8...1,3 N.M - na vijčani priključni blokovi matica Ø 6 mm 0,8...1,3 N.m - na vijčani priključni blokovi pozidiv broj 2
Vreme uključenja/isključenja	30...40 ms uključenje kalema i zatvaranje NO 10 ms isključenje kalema i otvaranje NO
Nivo sigurnosne pouzdanosti	B10d = 1369863 ciklusa kontaktor sa nazivnim opterećenjem u skladu sa EN/ISO 13849-1 B10d = 2000000 ciklusa kontaktor sa mehaničkim opterećenjem u skladu sa EN/ISO 13849-1
Mehanička trajnost	10 miliona ciklusa
Električna trajnost	1,3 Miliona ciklusa 6 A AC-3 pri U _e <= 440 V 1,3 Miliona ciklusa 6 A AC-3e pri U _e <= 440 V 0,05 miliona ciklusa 36 A AC-4 pri U _e <= 440 V
Visina	58 mm
Širina	45 mm
Dubina	57 mm
Masa proizvoda	0,225 kg

Okruženje

Standardi	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4
Sertifikacija proizvoda	CB Scheme[RETURN]CCC[RETURN]UL[RETURN]CSA[RETURN]EAC[RETURN]CE[RETURN]UL
Ip stepen zaštite	IP2x
Temperatura okoline za rad	-25...50 °C
Temperatura okoline za skladištenje	-50...80 °C
Nadmorska visina za rad uređaja	2000 m bez smanjenja karakteristika
Otpornost na plamen	V1 u skladu sa UL 94 Zahtev 2 u skladu sa NF F 16-101 Zahtev 2 u skladu sa NF F 16-102

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,600 cm
Package 1 Width	4,800 cm
Package 1 Length	6,200 cm
Package 1 Weight	219,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	9,202 kg
Unit Type of Package 3	P06
Number of Units in Package 3	640
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	157,220 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACh Deklaracija
REACh free of SVHC	Yes
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 months
-----------	-----------