



Tehničke karakteristike proizvoda Karakteristike

VCCF5

Vario - rastavljač za nužno isključenje- 125 A -
montaža na mont. ploču ili šinu

Osnovne informacije

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCCF
Product Type	Rastavljač za nužno isključenje

Dopunske informacije

Device Composition	Ručica Prekidač Produženje osovine
Mounting Support	Ručica: vrata Prekidač: simetrična šina Prekidač: ploča
Mounting Method	Sa 4 zavrtnja za ručica Stezaljka za prekidač Sa zavrtnjima bez matice za prekidač
Performance Level	Visoke performanse
Number of Poles	3P
Contact Type and Composition	3 NO
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	22 KW pri 230...240 V (AC-3) 30 KW pri 400...415 V (AC-3) 30 KW pri 690 V (AC-3) 37 KW pri 500 V (AC-3) 37 KW pri 690 V (AC-23A) 45 KW pri 500 V (AC-23A) 22 KW pri 230...240 V (AC-23A) 37 kW pri 400...415 V (AC-23A)
[Ie] Rated Operational Current	68,5 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	125 A
[Ithe] Conventional Enclosed Thermal Current	100 A
Making Capacity (I Rms)	1250 A pri 400 V AC-21A 1250 A pri 400 V AC-22A 1250 A pri 400 V AC-23A
Breaking Capacity	1000 A pri 400 V (AC-21A) 1000 A pri 400 V (AC-22A) 1000 A pri 400 V (AC-23A)
Rated Conditional Short Circuit Current	10 KA pri 400 V - odgovarajući osigurač 125 A aM 10 kA pri 400 V - odgovarajući osigurač 125 A gG
[Icm] Rated Short Circuit Making Capacity	2,8 kA pri 400 V na Ipeak
[Icw] Rated Short Time Withstand Current	1500 A pri 400 V 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV
Suitability for Isolation	Da
Network Type	DC AC

Intermittent Duty Class	30
Control Type	Zakretna ručica
Rotary Handle Mounting Style	Produžena
Handle Color	Crvena
Handle Front Plate Color	Žuta
Rotary Handle Padlocking	1 do 3 katanca 4...8 mm
Marking	0 - 1
Mechanical Durability	30000 ciklusa
Electrical Durability	30000 Ciklusa AC-21 30000 ciklusa DC-1...5
IEC Terminal Connection	Kolo napajanja: vijčani priključni blokovi kabl 95 mm ² - krutost kabla: jednožični Kolo napajanja: vijčani priključni blokovi kabl 70 mm ² - krutost kabla: fleksibilni - sa kablovskim završetkom
Tightening Torque	Kolo napajanja: 22,6 N.m - na vijčani priključni blokovi
Base Dimension	90 x 90 mm
Height	125 mm
Width	90 mm
Product Weight	1,32 kg

Okruženje

Standards	IEC 60947-3
Product Certifications	CCC[RETURN]UL[RETURN]CSA[RETURN]GL[RETURN]UKCA
Degree of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	TC
Mechanical Robustness	Vibracije 10...150 Hz (1 gn) u skladu sa IEC 60068-2-6 Udara 11 milisekundi (30 Gn) u skladu sa IEC 60068-2-27
Ambient Air Temperature for Operation	-20...50 °C
Fire Resistance	960 °C u skladu sa IEC 60695-2-1
Compatibility Code	Glavni rastavljač

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10,000 cm
Package 1 Width	11,500 cm
Package 1 Length	30,000 cm
Package 1 Weight	1,269 kg
Unit Type of Package 2	S03
Number of Units in Package 2	4
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	5,547 kg
Unit Type of Package 3	P06
Number of Units in Package 3	32
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	61,115 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	7f9d7799-4d0d-48a0-908b-7d323e11d373
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	257

Ugovorna garancija

Garancija	18 meseci
-----------	-----------