



### Main

|                               |   |
|-------------------------------|---|
| Range                         | MasterPacT  |
| Range of product              | MasterPact NW<br>MasterPact NW DC<br>MasterPact NW NAVY |
| Device short name             | MN  |
| Product or component type     | Voltage release   |
| Device application            | Control   |
| Voltage release type          | Opening coil<br>Undervoltage release                    |
| Control type                  | Standard  |
| [Uc] control circuit voltage  | 100...130 V AC 50/60 Hz<br>100...130 V DC               |
| Circuit breaker mounting mode | Drawout   |
| Range compatibility           | Masterpact MasterPact NW<br>Masterpact MasterPact NW DC |

### Complementary

|                      |  |
|----------------------|--|
| Operating threshold  | 0.35...0.7 x Un opening<br>0.85 Un closing |
| Response time        | 90 ms +/- 5 %                              |
| Supply holding power | 4.5 VA                                     |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3.0 cm  |
| Package 1 Width              | 8.0 cm  |
| Package 1 Length             | 6.0 cm  |
| Package 1 Weight             | 180.0 g |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.