



Main

Range	Vigilohm
Device short name	Cardew C
Product or component type	Surge limiter
Range compatibility	Vigilohm

Complementary

Rated voltage	440 V
Network rated voltage	380...660 V - AC (neutral distributed) 220...380 V - AC (neutral not distributed)
[Ui] rated insulation voltage	700...1100 V AC
Breaking capacity	40 kA AC at 50 Hz for 0.2 s
Net weight	1 kg
Width	70 mm
Height	160 mm
Depth	100 mm

Environment

Standards	NF C 15-100 NF C 63-150
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.200 cm
Package 1 Width	11.500 cm
Package 1 Length	17.000 cm
Package 1 Weight	685.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	16.966 kg
Unit Type of Package 3	P12
Number of Units in Package 3	96
Package 3 Height	50.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	76.800 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------