



Main

Range of product	Vigilohm
Device short name	XGR
Product or component type	Locating signal generator
Earthing system	IT

Complementary

Type of installation to be monitored	500 V - DC (between poles) 0...760 V - AC at 45...400 Hz (device connected to neutral) 0...440 V - AC at 45...400 Hz (device connected to phase)
Auxiliary supply voltage	220/240 V - AC at 50/60 Hz
Output frequency	2.5 Hz
Power consumption in VA	15 VA
Measurement current	2.5 mA
Internal impedance	40 kOhm
Material	Plastic
Net weight	0.85 kg
Height	59 mm
Width	108 mm
Depth	189 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	12.5 cm
Package 1 Length	27.5 cm
Package 1 Weight	1.346 kg
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.779 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------