



## Main

|                                    |                      |
|------------------------------------|----------------------|
| Range                              | Acti9                |
| Product or component type          | Comb busbar          |
| Mounting mode                      | Horizontal           |
| Accessory / separate part category | Connection accessory |
| Lines description                  | 1L                   |
| Length in 18 mm modules            | 24                   |

## Complementary

|                                |  |
|--------------------------------|--|
| Number of ways                 | 24 ways 1 L  |
| Poles configuration for 1 way  | 1 x 1P   |
| Connection pitch               | 18 mm  |
| Connector type                 | Tooth  |
| Distance between way           | 18 mm  |
| Marking                        | L  |
| Insulation                     | Insulated  |
| Device presentation            | Cuttable   |
| [Ie] rated operational current | 100 A at 40 °C   |
| [Ue] rated operational voltage | 415 V AC   |
| [Ui] rated insulation voltage  | 500 V AC conforming to IEC 61439-2   |
| Mounting location              | Top or bottom on tunnel type terminals<br>Top or bottom on double terminal   |
| 9 mm pitches                   | 48   |
| Width                          | 430 mm   |
| Colour                         | White (RAL 9003)   |
| Range compatibility            | Acti 9 Acti9 iC60<br>Acti 9 Acti9 iK60<br>Acti 9 Acti9 iLD<br>Acti 9 Acti9 iLD K<br>Acti 9 Acti9 iSW<br>Acti 9 Acti9 iSW-NA<br>Multi9 Multi9 C60 |

## Environment






|                         |   |
|-------------------------|---|
| Standards               | IEC 60947-7-1<br>IEC 61439-2                |
| Fire resistance         | 960 °C ( 30 s ) conforming to IEC 60695-2-1 |
| Pollution degree        | 3 conforming to IEC 60947-7-1               |
| IP degree of protection | IP20 with end-pieces and tooth covers       |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1 cm      |
| Package 1 Width              | 3.1 cm    |
| Package 1 Length             | 43.2 cm   |
| Package 1 Weight             | 99.8 g    |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 6.2 cm    |
| Package 2 Width              | 9 cm      |
| Package 2 Length             | 46.7 cm   |
| Package 2 Weight             | 1.118 kg  |
| Unit Type of Package 3       | S04       |
| Number of Units in Package 3 | 100       |
| Package 3 Height             | 30 cm     |
| Package 3 Width              | 40 cm     |
| Package 3 Length             | 60 cm     |
| Package 3 Weight             | 11.996 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>               |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|