



Main

| | |
|------------------------------------|----------------------|
| Range | Acti9 |
| Product or component type | Comb busbar |
| Mounting mode | Horizontal |
| Accessory / separate part category | Connection accessory |
| Lines description | 1L + N |
| Length in 18 mm modules | 24 |

Complementary

| | |
|--------------------------------|--|
| Number of ways | 12 ways N + 1 L |
| Poles configuration for 1 way | 1 x 1P + N 1 x 2P |
| Connection pitch | 18 mm |
| Connector type | Tooth |
| Distance between way | 36 mm |
| Marking | N L |
| Insulation | Insulated |
| Device presentation | Cuttable |
| [Ie] rated operational current | 100 A at 40 °C |
| [Ue] rated operational voltage | 415 V AC |
| [Ui] rated insulation voltage | 500 V AC conforming to IEC 61439-2 |
| Mounting location | Top or bottom on tunnel type terminals Top or bottom on double terminal |
| 9 mm pitches | 48 |
| Width | 430 mm |
| Colour | White (RAL 9003) |
| Range compatibility | Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW-NA Multi9 Multi9 C60 |






Environment

| | |
|-------------------------|---|
| Standards | IEC 60947-7-1 IEC 61439-2 |
| Fire resistance | 960 °C (30 s) conforming to IEC 60695-2-1 |
| Pollution degree | 3 conforming to IEC 60947-7-1 |
| IP degree of protection | IP20 with end-pieces and tooth covers |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.600 cm |
| Package 1 Width | 8.400 cm |
| Package 1 Length | 46.600 cm |
| Package 1 Weight | 166.000 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 5.600 cm |
| Package 2 Width | 8.400 cm |
| Package 2 Length | 46.600 cm |
| Package 2 Weight | 934.000 g |
| Unit Type of Package 3 | S04 |
| Number of Units in Package 3 | 55 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 40.000 cm |
| Package 3 Length | 60.000 cm |
| Package 3 Weight | 11.147 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|