



Main

Range	Affle Plus
Product or component type	Dimmer
Device presentation	Mechanism
Colour tint	White
Type of packing	Blister
Quantity per set	Set of 6
Sale per indivisible quantity	1
Load type	Halogen lamp - 50 W - 220 V AC Halogen lamp - 250 W - 220 V AC Incandescent lamp - 50 W - 220 V AC Incandescent lamp - 250 W - 220 V AC Low voltage halogen lamp with ferromagnetic transformer - 50 W - 220 V AC Low voltage halogen lamp with ferromagnetic transformer - 250 W - 220 V AC LED lamp - 3 W - 220 V AC LED lamp - 100 W - 220 V AC
Number of terminals	2

Complementary

Device mounting	Flush
Number of modules	1 module 50.3 x 42.6 mm
Actuator	Rotary
Fixing mode	Clip-in
Surface finish	Glossy
Dimmer control	300° rotary setting ON/OFF integrated
[Ie] rated operational current	0.22 A 1.13 A
[Ue] rated operational voltage	220 V AC 50/60 Hz
Screwdriver shape	Philips No 2
Clamping connection capacity	0.5...4 mm ² for rigid cable(s) 0.5...4 mm ² for stranded cable(s) 0.5...4 mm ² for flexible cable(s)
Wire stripping length	12...15 mm
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: cover Polycarbonate: button
Height	86 mm
Width	86 mm
Depth	45.5 mm
Embedding depth	25 mm
Net weight	0.095 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	0...50 °C
Standards	IEC 60669-2-1
IP degree of protection	IP20
Environmental characteristic	UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	135 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	810 g
Unit Type of Package 3	CAR
Number of Units in Package 3	72
Package 3 Height	21 cm
Package 3 Width	39.9 cm
Package 3 Length	46.9 cm
Package 3 Weight	10.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations