

APV9601

APC Easy UPS On-Line SRV Network Management Card, with direct SNMP connection



Overview

| | |
|--------------|--|
| Presentation | APV9601 NMC card allows for direct connection and control of an individual APC Easy UPS On-Line SRV UPS unit via SNMP. The configurable notification features keep you informed of detected problems as and when they occur. |
| Lead time | Usually in Stock |

Main

| | |
|---------------------------|---------------------------------|
| Product or component type | UPS network management cards |
| Provided equipment | CD with software User manual |

Physical

| | |
|---------------------|--------------------|
| Height | 2.5 cm |
| Width | 4.7 cm |
| Depth | 8 cm |
| Net weight | 0.11 kg |
| Mounting preference | No preference |
| Mounting mode | Not rack-mountable |

Conformance

| | |
|------------------------|----|
| Product certifications | CE |
|------------------------|----|

Environmental

| | |
|---------------------------------------|-------------------------|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % non-condensing |
| Ambient air temperature for storage | -15...45 °C |
| Storage Relative Humidity | 0...95 % non-condensing |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.2 cm |
| Package 1 Width | 13.2 cm |
| Package 1 Length | 16.8 cm |
| Package 1 Weight | 0.3 kg |

Offer Sustainability

| | |
|-----------------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Optimized Energy Efficiency | Energy efficient product |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|--------------------------|
| Warranty | 1 year repair or replace |
|----------|--------------------------|