

BK350EI

APC Back-UPS, 350VA/210W, Tower, 230V,
4x IEC C13 Outlets , User Replaceable Battery



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated power in W	210 W
Rated power in VA	350 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 60320 C14
Output connection type	3 IEC 60320 C13 1 IEC 60320 C13 surge 2 IEC Jumpers
Cable length	1.16 m
Number of cables	2
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Installation manual in japanese Detachable IEC power cord Detachable 1.2 m IEC power cord Telephone cable USB cable Warranty card

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	6 h
Number of battery replacement quantity	1
Battery voltage	12 V
Battery capacity	7.0 Ah
Battery charger power	14 W rated
Battery power in VAh	116 VAh capacity 84 VAh runtime
Battery life	4...6 year(s)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several v
Extended runtime	0

General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Colour	Beige
Height	16.5 cm
Width	9.1 cm
Depth	28.4 cm
Net weight	6.32 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Input voltage limits	180...266 V
Maximum input current	7 A
Switching current capacity	7 A

Output

Maximum configurable power in W	210 W
Output frequency	47...63 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
UPS type	Standby
Maximum configurable power in VA	350 VA
Transfer time	6 ms typical : 10 ms maximum

Conformance

Product certifications	C-Tick[RETURN]CE[RETURN]GOST[RETURN]VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Equipment protection policy	Lifetime : 100000 euros Lifetime : 50000 GBP

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.000000000...15240.000000000 m
Heat dissipation	19 Btu/h

Communications & Management

Free slots	0
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rate	310 J
Noise suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.000 cm
Package 1 Width	19.000 cm
Package 1 Length	41.500 cm
Package 1 Weight	6.435 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	70
Package 2 Height	142.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	492.450 kg
SCC14	10731304016349

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	019b51cf-d7f1-4f06-ac85-1378fc94c7aa
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Yes
Removable battery	User replaceable

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------