

BR1600MI  
APC Back-UPS Pro, 1600VA/960W, Tower,  
230V, 8x IEC C13 outlets, AVR, LCD, User  
Replaceable Battery



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated power in W	960 W
Rated power in VA	1600 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 60320 C13
Output connection type	6 IEC 60320 C13 2 IEC 60320 C13 surge
Battery type	Lead-acid battery

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	16 h
Number of battery replacement quantity	1
Battery voltage	24 V
Battery capacity	9.0 Ah
Battery charger power	11 W rated
Battery life	3...5 year(s)
Extended runtime	0

General

Provided equipment	User manual USB cable
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Physical

Colour	Black
Height	10 cm
Width	25 cm
Depth	38.2 cm
Net weight	10.9 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

## Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Input voltage limits	176...294 V
Maximum input current	10 A
Switching current capacity	10 A

## Output

Maximum configurable power in W	960 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains
UPS type	Line interactive
Maximum configurable power in VA	1600 VA

## Conformance

Product certifications	A-Tick[RETURN]C-Tick[RETURN]CE[RETURN]EAC[RETURN]RCM[RETURN]TISI
Marking	GS Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m
Acoustic level	45 dBA
Heat dissipation	21.5 Btu/h

## Communications & Management

Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm





## Surge Protection and Filtering

Surge energy rate	509 J
Noise suppression	Full time multi-pole noise filtering : 10% of IEEE surge let-through : zero clamping response time: instantaneous

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	22.5 cm
Package 1 Length	48.5 cm
Package 1 Weight	11.65 kg
SCC14	10731304346910

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace, 3 years repair or replace for European Union countries
----------	-----------------------------------------------------------------------------------