



Main

Product brand	Schneider Electric
Range	Wiser
Product or component type	Connected dimmer
Load type	Incandescent lamp Halogen lamp Fluorescent lamp LED lamp
Main colour tint	Dark grey

Complementary

Device presentation	Module
Load type	LED lamp: 5...100 VA at 230 V AC (RC LED mode) LED lamp: 5...20 VA at 230 V AC (RL LED mode) Incandescent lamp: 14...200 W at 230 V AC Halogen lamp: 14...150 W at 230 V AC LV halogen lamps: 14...200 VA at 12 V AC (electronic transformer) LV halogen lamps: 14...150 VA at 12 V AC (wound transformer)
Dimmer type	Universal
[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Standby consumption	< 0.4 W
Protection type	Overheating protection Short-circuit protection Automatic overload protection
Local signalling	Programming indication: LED (green/red/orange)
Connected auxiliaries	Maximum 10 auxiliary push-buttons
Cable length	50 m
Wiring configuration	Without neutral
Connections - terminals	Screw terminal
Clamping connection capacity	1.5...2.5 mm ² for solid cable(s) 1.5...2.5 mm ² for solid stranded cable(s)
Mounting support	Wall box
Embedding depth	19 mm
Width	43 mm
Height	43 mm

Environment

Ambient air temperature for operation	0...35 °C
IP degree of protection	IP20
Environmental characteristic	Indoor use
Operating altitude	<= 2000 m
Standards	EN 60669-2-5 IEC 60669-2-5 CE

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	80.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.72 kg
Unit Type of Package 3	P06
Number of Units in Package 3	960
Package 3 Height	105.0 cm
Package 3 Width	60.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	99.16 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information