

## Main

Product or component type	Switch
Device application	Control
Load type	Fluorescent lamps Small motor load Resistive Incandescent lamp Serial boost load (SBL)
Colour tint	Wood

## Complementary

Device presentation	Complete product
Rated current	20 A at 250 V AC 50/60 Hz
Switch function	2-pole 1-way
Number of gangs	2 gangs
Number of rocker	2
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 4 mm <sup>2</sup> for stranded cable(s) 1 x 6 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Brass terminal
Local signalling	On: LED indicator, LED (amber)
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator
Device mounting	Flush
Width	86 mm
Height	86 mm
Depth	32 mm

## Environment

IP degree of protection	IP20
Maximum ambient air temperature for operation	45 °C
Operating altitude	2000 m
Relative humidity	0...95 %
Standards	BS EN 60669-1 MS IEC 60669-1 SS 227-1 IEC 60669-1
Environmental characteristic	UV resistant

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm

Package 1 Weight	103.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.205 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	7.23 kg

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations