



### Main

Range	Acti9
Product name	Acti9 ID K
Product or component type	Residual current circuit breaker (RCCB)
Device short name	ID K
Poles description	4P
Neutral position	Left
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Quality labels	SAFETY Mark

### Complementary

Device location in system	Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	380...415 V AC 50 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 500 A Im 500 A
Rated conditional short-circuit current	GL63: Inc 4.5 kA K60: Inc 6 kA
[Ui] rated insulation voltage	440 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	No
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	81 mm
Width	72 mm
Depth	68 mm
Net weight	0.35 kg
Colour	White
Mechanical durability	5000 cycles
Electrical durability	AC-1: 4000 cycles
Connections - terminals	Biconnect top or bottom 1...35 mm <sup>2</sup> rigid Biconnect top or bottom 1...25 mm <sup>2</sup> flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN/IEC 61008-1 SS 97:part 1
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	2
Electromagnetic compatibility	8/20 $\mu$ s impulse withstand, 200 A conforming to EN/IEC 61008-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-25...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.2 cm
Package 1 Width	7.7 cm
Package 1 Length	8.4 cm
Package 1 Weight	0.35 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	9 cm
Package 2 Width	8.5 cm
Package 2 Length	22 cm
Package 2 Weight	1.438 kg
Unit Type of Package 3	S03
Number of Units in Package 3	27
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	13.442 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations