



### Main

Range of product	Acti9
Product name	Acti9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	iPRD8
Device application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
Poles description	1P
Remote signalling	Without
Surge arrester type	Electrical distribution network
Earthing system	TN-C IT 230

### Complementary

Surge arrester class type	Type 2 + 3
Surge arrester technology	MOV
[Ue] rated operational voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] nominal discharge current	Common mode: 2.5 kA (L/PE) Common mode: 2.5 kA (N/PE)
[Imax] maximum discharge current	Common mode: 8 kA L/PE
[Uoc] open circuit voltage	10 kV type 3 common mode L/PE
[Uc] maximum continuous operating voltage	Common mode: 350 V L/PE Common mode: 350 V N/PE
Maximum [Up] voltage protection level	Common mode <1 kV type 2 L/PE Common mode <1 kV type 3 L/PE
[Ut] temporary overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode
Disconnecter device type	Associated circuit breaker iC60L 10 A curve C - Icu 25 kA[RETURN]Associated circuit breaker IC60N 10 A curve C - Icu 10 kA[RETURN]Associated circuit breaker iC60H 10 A curve C - Icu 15 kA[RETURN]Associated fuse gG 25 A - Icu 15 kA[RETURN]Associated fuse gG 80 A - Icu 50 kA
Mounting mode	Clip-on (DIN rail)
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	69 mm
Net weight	0.11 kg
Colour	White (RAL 9003)
[Ipe] Ground residual current	0.003 MA 0.6 mA
Connections - terminals	Tunnel type terminal (downside) 2.5...35 mm <sup>2</sup> Tunnel type terminal (upside) 2.5...35 mm <sup>2</sup>
Tightening torque	2.5 N.m



## Environment

IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	7.2 cm
Package 1 Length	9.2 cm
Package 1 Weight	129 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	10 cm
Package 2 Length	28 cm
Package 2 Weight	1.635 kg
Unit Type of Package 3	S03
Number of Units in Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	15.229 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------