



Main

Range of product	TeSys Deca
Device short name	GV2DM
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 1
Poles description	3P
Utilisation category	AC-3
Motor power kW	0.75 kW at 400/415 V AC 50/60 Hz 0.75 kW at 440 V AC 50/60 Hz 1.1 kW at 440 V AC 50/60 Hz 1.1 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Magnetic tripping current	33.5 A

Complementary

Device composition	1 combination block GV2AF3 1 3-pole contactor 1 motor circuit breaker type GV2ME
Thermal protection adjustment range	1.6...2.5 A
Rated breaking capacity	Iq 50 kA at 400/415 V conforming to IEC 60947-4-1 Iq 50 kA at 440 V conforming to IEC 60947-4-1 Iq 50 kA at 500 V conforming to IEC 60947-4-1
Net weight	0.596 kg
Height	176.4 mm
Width	45 mm
Depth	99.6 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	19.6 cm
Package 1 Length	5.4 cm
Package 1 Weight	600.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Circularity Profile

 [End Of Life Information](#)

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty

18 months
