



Main

Range of product	Acti9
Product name	Acti9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	iPRD8
Device application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	KEMA-KEUR NF
Poles description	2P
Remote signalling	Without
Surge arrester type	Electrical distribution network
Earthing system	TN-C-S

Complementary

Surge arrester class type	Type 2 + 3
Surge arrester technology	MOV
[Ue] rated operational voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] nominal discharge current	Common mode: 2.5 kA (L/PE) Common mode: 2.5 kA (N/PE)
[Imax] maximum discharge current	Common mode: 8 kA L/PE Common mode: 8 kA N/PE
[Uoc] open circuit voltage	10 kV type 3 common mode L/PE 10 kV type 3 common mode N/PE
[Uc] maximum continuous operating voltage	Common mode: 350 V L/PE Common mode: 350 V N/PE
Maximum [Up] voltage protection level	Common mode <1 kV type 2 L/PE Common mode <1 kV type 2 N/PE Common mode <1 kV type 3 L/PE Common mode <1 kV type 3 N/PE
[Ut] temporary overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode
Disconnecter device type	Associated circuit breaker iC60L 10 A curve C - Icu 25 kA[RETURN]Associated circuit breaker IC60N 10 A curve C - Icu 10 kA[RETURN]Associated circuit breaker iC60H 10 A curve C - Icu 15 kA[RETURN]Associated fuse gG 25 A - Icu 15 kA[RETURN]Associated fuse gG 80 A - Icu 50 kA
Mounting mode	Clip-on (DIN rail)
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	69 mm
Net weight	0.216 kg
Colour	White (RAL 9003)
[Ipe] Ground residual current	0.6 MA 0.003 mA
Connections - terminals	Tunnel type terminal (downside) 2.5...35 mm² Tunnel type terminal (upside) 2.5...35 mm²
Tightening torque	2.5 N.m




Environment

IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	7.2 cm
Package 1 Length	9 cm
Package 1 Weight	246 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	9.8 cm
Package 2 Width	8.5 cm
Package 2 Length	28 cm
Package 2 Weight	1.56 kg
Unit Type of Package 3	S03
Number of Units in Package 3	54
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14.553 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------