



Main

Range	Acti9
Product name	Acti9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	iID
Poles description	2P
Neutral position	Left
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	100 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	I _{dm} 1500 A I _m 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	91 mm
Width	36 mm
Depth	73.5 mm
Net weight	0.21 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	AC-1: 15000 cycles
Locking options description	Padlocking device
Connections - terminals	Single terminal top or bottom 1...35 mm ² rigid Single terminal top or bottom 1...25 mm ² flexible Single terminal top or bottom 1...25 mm ² flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN/IEC 61008-1
Product certifications	EAC
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61008-1
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	8.200 cm
Package 1 Length	9.800 cm
Package 1 Weight	210.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	54
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.960 kg
Unit Type of Package 3	P12
Number of Units in Package 3	432
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	107.680 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------