



Main

Range	Vigilohm
Device short name	IM20-1700
Product or component type	Network adaptor subassembly
Device application	Medium network
Range compatibility	Vigilohm Vigilohm IM IM20 insulation monitoring device Vigilohm Vigilohm IM IM20L insulation monitoring device

Complementary

Network rated voltage	600...1700 V - AC (neutral distributed) 440...1000 V - AC (neutral not distributed) 345...1000 V - DC
Average impedance	400 kOhm
Maximum distance to	IM20: 3 m
Net weight	0.2 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	8 cm
Package 1 Length	9.5 cm
Package 1 Weight	150 g
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.018 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------