



### Main

Range	Vivace
Product or component type	Switched socket
Device short name	KB25
Device presentation	Complete product
Main colour tint	White
Colour tint	White

### Complementary

Pilot light	Red neon indicator
Outlet poles configuration	2P + E
Number of gangs	2 gangs
Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	120.6 mm
Embedding depth	35 mm
Rated current	13 A at 250 V AC, resistive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L N Earth
Tightening torque	0.4 N.m
Clamping connection capacity	2 x 4 mm <sup>2</sup> 3 x 2.5 mm <sup>2</sup>
Width	147 mm
Height	87 mm
Depth	35 mm






### Environment

Standards	MS 589 SS 145 BS 1363
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	14.6 cm
Package 1 Weight	148 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	5 cm
Package 2 Weight	875 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8750 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------