



Main

| | |
|---------------------------|----------------------|
| Range | Vivace |
| Product or component type | Switched socket |
| Device short name | KB25 |
| Device application | Power supply Control |
| Device presentation | Complete product |
| Switch application | On/off switching |
| Main colour tint | White |
| Colour tint | White |

Complementary

| | |
|------------------------------|---|
| Outlet poles configuration | 2P + E |
| Number of gangs | 2 gangs |
| Colour tint | White |
| Material | Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base |
| Projecting depth | 8 mm |
| Device mounting | Flush |
| Mounting support | Wall mounted |
| Fixing mode | By screw M3.5 |
| Fixing center | 120.6 mm |
| Embedding depth | 22.0 mm |
| Rated current | 13 A at 250 V AC, resistive |
| Network frequency | 50/60 Hz |
| Contacts material | Brass and phosphor bronze |
| Connections - terminals | Pillar terminal |
| Terminal identifier | Earth L N |
| Tightening torque | 0.4 N.m |
| Clamping connection capacity | 3 x 2.5 mm ² 2 x 4 mm ² |
| Width | 147 mm |
| Height | 87 mm |
| Depth | 35 mm |

Environment

| | |
|---------------------------------------|-------------------------------|
| Standards | MS 589 BS 1362-2 SS 145 |
| Ambient air temperature for operation | 0...40 °C |
| Ambient air temperature for storage | -5...60 °C |
| Relative humidity | 0...95 % |
| Operating altitude | <= 2000 m |
| Environmental characteristic | Indoor use |
| IP degree of protection | IP20 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.1 cm |
| Package 1 Width | 8.6 cm |
| Package 1 Length | 14.6 cm |
| Package 1 Weight | 148 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 19 cm |
| Package 2 Weight | 738 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 50 |
| Package 3 Height | 21 cm |
| Package 3 Width | 31.5 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 8.4 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|