



Main

Range	Vivace
Device short name	KB30
Product or component type	Fuse connection unit
Device application	Power supply
Device presentation	Complete mechanism
Main colour tint	White
Colour tint	Wall: white

Complementary

Colour tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting depth	8 mm
Device mounting	Surface Flush
Mounting support	Wall mounted
Fixing mode	By screw M3.5
Fixing center	60.3 mm
Embedding depth	35 mm
Rated current	13 A at 250 V AC, resistive
Network frequency	50 Hz
Contacts material	Brass and phosphor bronze
Connections - terminals	Pillar terminal
Terminal identifier	L in L out N in N out Earth
Tightening torque	0.4 N.m
Clamping connection capacity	2 x 4 mm ² power circuit 3 x 2.5 mm ² incoming 1 x 1.5 mm ² outgoing 1 x 2.5 mm ² input
Width	87 mm
Height	87 mm
Depth	35 mm





Environment

Standards	BS 1363-4
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Operating altitude	0...2000 m
Environmental characteristic	Indoor use
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.5 cm
Package 1 Length	14.6 cm
Package 1 Weight	116.9 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.239 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	11940 g

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------