



Main

Product or component type	USB charger + switched socket
Fixing mode	By screws

Complementary

Outlet standard	British
Outlet standard description	With earthing contact
Integrated connection type	2 USB type A 5 V DC 2.1 A 1 socket-outlet 250 V AC 13 A 50/60 Hz
Device mounting	Surface
Device presentation	Complete product
Mounting support	Mounting box
Outlet poles configuration	3P with shutter
Colour tint	Wine gold
Surface finish	Matt
Surface treatment	Painted
Type of packing	Flow-pack
Quantity per set	Set of 10
Ambient air temperature for storage	-5...60 °C
Protection type	Current protection Thermal protection
Dielectric strength	2000 V
Ambient air temperature for operation	0...40 °C
Service life in cycles	5000 cycles
Connections - terminals	Screw terminal
Number of terminals	3
Screwdriver shape	Phillips combined
Number of cables	2
Clamping connection capacity	1.5...4 mm ² for rigid cable(s) 1.5...4 mm ² for stranded cable(s) 1.5...4 mm ² for flexible cable(s)
Material	PC (polycarbonate): grid plate PC (polycarbonate): surround
Wire stripping length	12 mm
Height	86 mm
Width	86 mm
Depth	38.2 mm
Embedding depth	29.3 mm
Standards	UL 1310 UL 498 UL 94

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	109.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.09 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6.54 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile