



## Main

|                           |                               |
|---------------------------|-------------------------------|
| Product or component type | USB charger + switched socket |
| Fixing mode               | By screws                     |

## Complementary

|                                       |  |
|---------------------------------------|--|
| Outlet standard deviation             | British  |
| Outlet standard description           | With earthing contact  |
| Integrated connection type            | 2 USB type A 5 V DC 2.1 A<br>1 socket-outlet 250 V AC 13 A 50/60 Hz  |
| Device mounting                       | Surface  |
| Device presentation                   | Complete product   |
| Mounting support                      | Mounting box   |
| Outlet poles configuration            | 3P with shutter  |
| Colour tint                           | Wine gold  |
| Surface finish                        | Matt   |
| Surface treatment                     | Painted  |
| Type of packing                       | Flow-pack  |
| Quantity per set                      | Set of 10  |
| Ambient air temperature for storage   | -5...60 °C   |
| Protection type                       | Current protection<br>Thermal protection   |
| Dielectric strength                   | 2000 V   |
| Ambient air temperature for operation | 0...40 °C  |
| Service life in cycles                | 5000 cycles  |
| Connections - terminals               | Screw terminal   |
| Number of terminals                   | 3  |
| Screwdriver shape                     | Phillips combined  |
| Number of cables                      | 2  |
| Clamping connection capacity          | 1.5...4 mm <sup>2</sup> for rigid cable(s)<br>1.5...4 mm <sup>2</sup> for stranded cable(s)<br>1.5...4 mm <sup>2</sup> for flexible cable(s) |
| Material                              | PC (polycarbonate): grid plate<br>PC (polycarbonate): surround   |
| Wire stripping length                 | 12 mm  |
| Height                                | 86 mm  |
| Width                                 | 86 mm  |
| Depth                                 | 38.2 mm  |
| Embedding depth                       | 29.3 mm  |
| Standards                             | UL 1310<br>UL 498<br>UL 94   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.



## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP20 |
|-------------------------|------|

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3.4 cm  |
| Package 1 Width              | 8.6 cm  |
| Package 1 Length             | 8.6 cm  |
| Package 1 Weight             | 109.0 g |
| Unit Type of Package 2       | BB1     |
| Number of Units in Package 2 | 10      |
| Package 2 Height             | 9.5 cm  |
| Package 2 Width              | 19.0 cm |
| Package 2 Length             | 19.5 cm |
| Package 2 Weight             | 1.09 kg |
| Unit Type of Package 3       | CAR     |
| Number of Units in Package 3 | 60      |
| Package 3 Height             | 21.0 cm |
| Package 3 Width              | 30.0 cm |
| Package 3 Length             | 39.5 cm |
| Package 3 Weight             | 6.54 kg |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |