



## Main

Product or component type	Dimmer
Device presentation	Complete product
Provided equipment	Screws
Dimmer application	Capacitive load Inductive load Ohmic load
Dimmer control	Rotary push type
Load type	Incandescent lamps - 50...250 W - 220...240 V AC High voltage halogen lamp - 50...250 W - 220...240 V AC Electronic transformer - 50...250 VA Dimmable LED - 3...100 W
Colour tint	White
Type of packing	Carton
Quantity per set	Set of 8
Market segment	Small commercial Residential

## Complementary

[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Protection type	Thermal fuse Surge arrester
Actuator	Knob
Fixing mode	By screws
Clamping connection capacity	<= 2 x 2.5 mm <sup>2</sup> for flexible cable(s) <= 2 x 2.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	12 mm
Material	Polycarbonate: plastic part Brass: terminals Steel coated with zinc chromate: terminal screw
Device mounting	Flush
Height	86 mm
Width	86 mm
Embedding depth	35 mm

## Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	10...95 %
Environmental characteristic	Oil and vapour resistant
Standards	IEC 60669-2-1 CE

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.63 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	125.6 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.105 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	48
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	7128.8 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>