



## Main

|                            |                  |
|----------------------------|------------------|
| Range                      | AvatarOn         |
| Product or component type  | Switched socket  |
| Device application         | Power supply     |
| Device presentation        | Complete product |
| Outlet poles configuration | 3P with shutter  |
| Type of packing            | Flow-pack        |

## Complementary

|                                |  |
|--------------------------------|--|
| Rated current                  | 13 A socket-outlet                                   |
| [Ue] rated operational voltage | 250 V AC 50/60 Hz                                    |
| Socket number                  | 2  |
| Outlet standard description    | With earthing contact                                |
| Outlet standard                | British BS 1363A                                     |
| Number of gangs                | 2 gangs  |
| Service life in cycles         | 20000 cycles   |
| Electrical durability          | 5000 cycles  |
| Connections - terminals        | Screw terminal                                       |
| Material                       | Polycarbonate: grid plate<br>Polycarbonate: surround |
| Surface finish                 | Glossy   |
| Surface treatment              | Painted mechanism cover                              |
| Device mounting                | Surface  |
| Fixing mode                    | Screw  |
| Height                         | 86 mm  |
| Width                          | 146 mm   |
| Depth                          | 31.7 mm  |

## Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| IP degree of protection               | IP20                        |
| Ambient air temperature for operation | -5...45 °C                  |
| Ambient air temperature for storage   | -5...60 °C                  |
| Relative humidity                     | 0...95 %                    |
| Standards                             | MS 589<br>BS 1363<br>SS 145 |
| Product certifications                | SIRIM                       |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 3.2 cm   |
| Package 1 Width              | 8.6 cm   |
| Package 1 Length             | 14.6 cm  |
| Package 1 Weight             | 152 g    |
| Unit Type of Package 2       | BB1      |
| Number of Units in Package 2 | 7        |
| Package 2 Height             | 9.5 cm   |
| Package 2 Width              | 19 cm    |
| Package 2 Length             | 19.5 cm  |
| Package 2 Weight             | 1.121 kg |
| Unit Type of Package 3       | CAR      |
| Number of Units in Package 3 | 42       |
| Package 3 Height             | 21 cm    |
| Package 3 Width              | 30 cm    |
| Package 3 Length             | 39.5 cm  |
| Package 3 Weight             | 7847 g   |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations      |