



## Main

Range of product	TeSys Deca
Device short name	GV2DM
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 1
Poles description	3P
Utilisation category	AC-3
Motor power kW	5.5 kW at 400/415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz 7.5 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Magnetic tripping current	170 A

## Complementary

Device composition	1 combination block GV2AF3 1 3-pole contactor 1 motor circuit breaker type GV2ME
Thermal protection adjustment range	9...14 A
Rated breaking capacity	Iq 15 kA at 400/415 V conforming to IEC 60947-4-1 Iq 8 kA at 440 V conforming to IEC 60947-4-1 Iq 6 kA at 500 V conforming to IEC 60947-4-1
Net weight	0.601 kg
Height	176.4 mm
Width	45 mm
Depth	99.6 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	19.6 cm
Package 1 Length	5.4 cm
Package 1 Weight	660.0 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

Circularity Profile

 [End Of Life Information](#)

---

WEEE

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

### Contractual warranty

---

Warranty

18 months

---