



Main

Range of product	TeSys Deca
Device short name	GV2DM
Product or component type	Motor starter
Motor starter type	Non reversing
Coordination type	Type 1
Poles description	3P
Utilisation category	AC-3
Motor power kW	9 kW at 400/415 V AC 50/60 Hz 11 kW at 440 V AC 50/60 Hz 11 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Magnetic tripping current	327 A

Complementary

Device composition	1 3-pole contactor 1 motor circuit breaker type GV2ME 1 combination block GV2AF3
Thermal protection adjustment range	17...23 A
Rated breaking capacity	Iq 15 kA at 400/415 V conforming to IEC 60947-4-1 Iq 6 kA at 440 V conforming to IEC 60947-4-1 Iq 4 kA at 500 V conforming to IEC 60947-4-1
Net weight	0.646 kg
Height	186.8 mm
Width	45 mm
Depth	105.9 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	10.5 cm
Package 1 Length	19.6 cm
Package 1 Weight	967.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty

18 months
