

## Main

|  |   |
|--|---|
| Range  | Linergy                                       |
| Product name   | FT  |
| Device short name  | GV2G  |
| Product or component type                                | Comb busbar                                   |
| Accessory / separate part category                       | Connection accessory                          |
| Poles description  | 3P  |
| Range compatibility                                      | TeSys Deca<br>TeSys GV2<br>TeSys K<br>TeSys U |
| Number of tap-offs                                       | 4   |
| [I <sub>th</sub> ] conventional free air thermal current | 63 A  |
| Connection pitch   | 45 mm   |

## Complementary

|                              |             |
|------------------------------|-------------|
| Mounting location            | On terminal |
| [U] rated insulation voltage | 690 V       |
| Length                       | 179 mm      |
| Net weight                   | 0.077 kg    |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 1.000 cm   |
| Package 1 Width              | 3.500 cm   |
| Package 1 Length             | 18.000 cm  |
| Package 1 Weight             | 78.000 g   |
| Unit Type of Package 2       | S01        |
| Number of Units in Package 2 | 60         |
| Package 2 Height             | 15.000 cm  |
| Package 2 Width              | 15.000 cm  |
| Package 2 Length             | 40.000 cm  |
| Package 2 Weight             | 4.930 kg   |
| Unit Type of Package 3       | P06        |
| Number of Units in Package 3 | 1920       |
| Package 3 Height             | 75.000 cm  |
| Package 3 Width              | 60.000 cm  |
| Package 3 Length             | 80.000 cm  |
| Package 3 Weight             | 165.460 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.


## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | <a href="#">End Of Life Information</a>       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sets of Busbars GV2G445, GV2G454, GV2G472, with Terminal Block GV2G05



|                     | l   | p  |
|---------------------|-----|----|
| GV2G445 (4 x 45 mm) | 179 | 45 |
| GV2G454 (4 x 54 mm) | 206 | 54 |
| GV2G472 (4 x 72 mm) | 260 | 72 |

| Number of tap-offs | a   |     |     |     |
|--------------------|-----|-----|-----|-----|
|                    | 5   | 6   | 7   | 8   |
| GV2G445            | 224 | 269 | 314 | 359 |
| GV2G454            | 260 | 314 | 368 | 422 |
| GV2G472            | 332 | 404 | 476 | 548 |