

Main

Range	TeSys
Device short name	GV4A
Product or component type	Auxiliary contact block
Device application	Signalling
Range compatibility	TeSys TeSys GV4 multifunction circuit breaker
Mounting location	Right side
Mounting mode	Clipped
Pole contact composition	2 NO + 2 NC

Complementary

[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
[Ue] rated operational voltage	24...250 V AC 24...250 V DC
[Ith] conventional free air thermal current	5 A
Associated fuse rating	5 A gG conforming to IEC 60947-5-1
Mechanical durability	100000 cycles
Minimum switching current	2 mA
Minimum switching voltage	17 V
Rated operational power in VA	400 VA at 230...240 V AC-12
Rated operational power in W	50 W at 24 V DC-12


Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	9 cm
Package 1 Length	15.6 cm
Package 1 Weight	150 g
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3 kg

Offer Sustainability

Packaging without single use plastic	Yes
Packaging made with recycled cardboard	Yes
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No