



Main

Range	TeSys
Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	TeSys TeSys GV4 TeSys TeSys BV4
Voltage release type	Undervoltage release
[Uc] control circuit voltage	220...240 V AC 50 Hz 208...240 V AC 60 Hz

Complementary

[Ui] rated insulation voltage	240 V conforming to IEC 60947-1
Threshold tripping voltage	< 0.35 Un failsafe opening 0.35...0.7 Un possible opening 0.85...1.1 Un enabled closing
Mounting mode	Internal mounting
Maximum inrush power in VA	7 VA
Maximum hold-in power consumption in VA	7 VA
Mechanical durability	20000 cycles
Operating time	< 50 ms
Connections - terminals	Spring terminals 1 0.5...1.5 mm ² - cable stiffness: flexible without cable end
Wire stripping length	8 mm



Environment

Quantity per set	Set of 1
------------------	----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	6.2 cm
Package 1 Length	8.6 cm
Package 1 Weight	64.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	8.8 cm
Package 2 Width	13.2 cm
Package 2 Length	18.6 cm
Package 2 Weight	690.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.4 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins