



## Main

Range	TeSys
Product or component type	Rotary handle
Device short name	GV6AP
Range compatibility	TeSys TeSys GV6 motor circuit breaker
Accessory / separate part category	Control accessory
Handle colour	Black
Handle front plate colour	Black
Rotary handle mounting location	Front
Rotary handle mounting style	Direct

## Complementary

Rotary handle padlocking	1 to 3 padlocks 5...8 mm Padlock in OFF position
Net weight	0.45 kg

## Environment

IP degree of protection	IP40
IK degree of protection	IK07

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	15.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	504.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	11.05 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	141.396 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------