

LC1DLKP7

Capacitor contactor, Tesys Deca, 20kVAR at 400/415V 50Hz, 230V AC 50/60Hz coil, screw clamp terminals





Main

Range	TeSys TeSys Deca
Product name	TeSys LC1D.K TeSys Deca
Product or component type	Capacitor duty contactor
Device short name	LC1DLK
Device application	Control
Contact application	Power factor correction
Utilisation category	AC-6b
Poles description	3P
Power pole contact composition	3 NO
Device location in system	Inside delta interruption Line interruption
[Ue] rated operational voltage	Power circuit: 690 V AC 50/60 Hz
Reactive power rating	11 Kvar at 230 V AC 50 Hz 60 °C 20 Kvar at 400 V AC 50 Hz 60 °C 21 Kvar at 440 V AC 50 Hz 60 °C 33 kvar at 690 V AC 50 Hz 60 °C
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	230 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 2 NC instantaneous
Electrical durability	300000 Cycles at Ue 400 V 200000 cycles at Ue 690 V
Mounting support	DIN rail Plate
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 IEC 60335-1
Product certifications	IECEE CB Scheme[RETURN]UKCA
Connections - terminals	Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 2.5...16 mm ² - cable stiffness: solid Power circuit: screw clamp terminals 2 2.5...6 mm ² - cable stiffness: solid Power circuit: screw clamp terminals 1 1.5...10 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 1.5...6 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 1...10 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible with cable end
Tightening torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 2.5 N.m - on screw clamp terminals
Maximum operating rate	240 cyc/h

Complementary

Auxiliary contacts type

Type mechanically linked 1 NO + 2 NC conforming to IEC 60947-5-1

Environment

IP degree of protection	IP20 front face conforming to IEC 60529
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	0...3000 m
Height	125 mm
Width	45 mm
Depth	127 mm
Net weight	0.6 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.700 cm
Package 1 Width	19.400 cm
Package 1 Length	22.700 cm
Package 1 Weight	610.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.167 kg
Unit Type of Package 3	P06
Number of Units in Package 3	48
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	43.484 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------