

LC1G6304LSEA

High power contactor, TeSys Giga
630,4P(4NO),AC-1 ≤ 440 V 1050A,advanced
version,200-500V AC/DC wide band coil



Main

Range	TeSys
Range of product	TeSys Giga
Product or component type	Contacteur
Device short name	LC1G
Contacteur application	Power switching
Utilisation category	AC-3 AC-3e AC-1 AC-5a AC-5b AC-6a AC-6b DC-1 DC-3 DC-5
Poles description	4P
[Ue] rated operational voltage	≤ 1000 V AC 50/60 Hz ≤ 460 V DC
[Ie] rated operational current	630 A (at ≤ 60 °C) at ≤ 440 V AC-3 1050 A (at ≤ 40 °C) at ≤ 1000 V AC-1
[Uc] control circuit voltage	200...500 V AC 50/60 Hz 200...500 V DC
Control circuit voltage limits	Operational: 0.8 Uc Min...1.1 Uc Max (at ≤ 60 °C) Drop-out: 0.1 Uc Max...0.45 Uc Min (at ≤ 60 °C)

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overtension category	III
[Ith] conventional free air thermal current	1050 A (at 40 °C)
Rated breaking capacity	5550 A at 440 V
[Icw] rated short-time withstand current	5.05 KA - 10 s 4.4 KA - 30 s 3.4 KA - 1 min 2.2 KA - 3 min 1.6 kA - 10 min
Associated fuse rating	630 A aM at ≤ 440 V for motor 500 A aM at ≤ 690 V for motor 1250 A gG at ≤ 690 V
Average impedance	0.000065 Ohm
[Ui] rated insulation voltage	1000 V
Power dissipation per pole	70 W AC-1 - Ith 1050 A 26 W AC-3 - Ith 630 A
Compatibility code	LC1G
Pole contact composition	4 NO
Auxiliary contact composition	1 NO + 1 NC
Irms rated making capacity	7220 A at 440 V
Coil technology	Built-in bidirectional peak limiting
Safety reliability level	B10d = 100000 cycles contacteur with nominal load conforming to EN/ISO 13849-1 B10d = 1800000 cycles contacteur with mechanical load conforming to EN/ISO 13849-1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mechanical durability	5 Mcycles
Inrush power in VA (50/60 Hz, AC)	670 VA
Inrush power in W (DC)	390 W
Hold-in power consumption in VA (50/60 Hz, AC)	17.0 VA
Hold-in power consumption in W (DC)	11.0 W
Operating time	40...70 ms closing 15...50 ms opening
Maximum operating rate	600 Cyc/H AC-3 600 Cyc/H AC-3e 300 cyc/h AC-1
Connections - terminals	Power circuit: bar 2 - busbar cross section: 52 x 20 mm Power circuit: lugs-ring terminals 1 185 mm ² Power circuit: bolted connection Control circuit: push-in 1 0.2...2.5 mm ² - cable stiffness: solid stranded without cable end Control circuit: push-in 1 0.25...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: push-in 2 0.5...1.0 mm ² with cable end Control circuit: push-in 0.75...2.5 mm ² - cable stiffness: solid stranded without cable end Control circuit: push-in 0.75...2.5 mm ² - cable stiffness: flexible with cable end
Connection pitch	70 mm
Mounting support	Plate
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1 JIS C8201-5-1 UL 60335-1 UL 60335-2-40:Annex JJ
Product certifications	CB Scheme[RETURN]CCC[RETURN]cULus[RETURN]EAC[RETURN]CE[RETURN]UKCA[RETURN] RO-MR by DNV-GL
Tightening torque	58 N.m
Height	388.5 mm
Width	281 mm
Depth	266 mm
Net weight	22 kg

Environment

IP degree of protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-60...80 °C
Mechanical robustness	Vibrations 5...300 Hz 2 gn contactor open Vibrations 5...300 Hz 4 gn contactor closed Shocks 10 gn 11 ms contactor open Shocks 15 gn 11 ms contactor closed
Colour	Dark grey
Protective treatment	TH
Permissible ambient air temperature around the device	-40...70 °C at U _c

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	35 cm
Package 1 Width	37 cm
Package 1 Length	50 cm
Package 1 Weight	24.1 kg
Unit Type of Package 2	S06
Number of Units in Package 2	2
Package 2 Height	83 cm

Package 2 Width	60.0 cm
Package 2 Length	80.0 cm
Package 2 Weight	51.3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

