

LC1DWK12M7

Capacitor contactor, Tesys Deca, 63kVAR at 400/415V 50Hz, 220V AC 50/60Hz coil, screw clamp terminals



Main

Range	TeSys
Product name	TeSys LC1D.K TeSys Deca
Product or component type	Capacitor duty contactor
Device short name	LC1DVK
Device application	Control
Contactor application	Power factor correction
Utilisation category	AC-6b
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit: 690 V AC 50/60 Hz
Reactive power rating	35 Kvar at 230 V AC 50 Hz 60 °C 63 Kvar at 400 V AC 50 Hz 60 °C 67 Kvar at 440 V AC 50 Hz 60 °C 104 Kvar at 690 V AC 50 Hz 60 °C 30 Kvar at 230 V AC 60 Hz 60 °C 60 Kvar at 460 V AC 60 Hz 60 °C 80 kvar at 575 V AC 60 Hz 60 °C
Control circuit type	AC at 50/60 Hz
[Uc] control circuit voltage	220 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 2 NC instantaneous
Electrical durability	300000 Cycles at Ue 400 V 200000 cycles at Ue 690 V
Mounting support	DIN rail Plate
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product certifications	IECEE CB Scheme[RETURN]UL[RETURN]CSA[RETURN]UKCA
Connections - terminals	Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Power circuit: connector 1 4...50 mm ² - cable stiffness: solid Power circuit: connector 2 4...25 mm ² - cable stiffness: solid Power circuit: connector 1 4...50 mm ² - cable stiffness: flexible without cable end Power circuit: connector 2 4...25 mm ² - cable stiffness: flexible without cable end Power circuit: connector 1 4...50 mm ² - cable stiffness: flexible with cable end Power circuit: connector 2 4...16 mm ² - cable stiffness: flexible with cable end
Tightening torque	Power circuit: 9 N.m - on connector Control circuit: 1.7 N.m - on screw clamp terminals
Maximum operating rate	240 cyc/h

Complementary

Auxiliary contacts type

Type mechanically linked 1 NO + 2 NC conforming to IEC 60947-5-1

Environment

IP degree of protection	IP20 front face conforming to IEC 60529
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Operating altitude	0...3000 m
Height	180 mm
Width	85 mm
Depth	154 mm
Net weight	1.65 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.000 cm
Package 1 Width	13.200 cm
Package 1 Length	17.000 cm
Package 1 Weight	1.786 kg
Unit Type of Package 2	S06
Number of Units in Package 2	48
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	95.368 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------