

MVS08H4MW2L

Circuit breaker, EasyPact MVS, 800A, 65KA, 4 Poles, MDO, ET2I



Main

Range	EasyPact
Product name	MVS08H
Device short name	MVS08H
Product or component type	Circuit breaker
Device application	Distribution
Poles description	4P
Protected poles description	4P 4d
[In] rated current	800 A at 40 °C
Network type	AC
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity code	H
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category B
Trip unit name	MicroLogic 2.0
Trip unit technology	Electronic
Trip unit rating	800 A

Complementary

Network frequency	50/60 Hz
Control type	Manually operated
Mounting mode	Drawout
Mounting support	Base plate Rail
Connection position	Vertical Horizontal
Location of connection	Rear
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	12 kV conforming to IEC 60947-2
Circuit breaker CT rating	800 A
Breaking capacity	50 KA Icu at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 690 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	65 KA (Ics) at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 50 kA (Ics) at 690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	20000 Cycles (with maintenance) conforming to IEC 60947-2 10000 cycles (without maintenance) conforming to IEC 60947-2
Electrical durability	Category B: 5000 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 Category B: 5000 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
Connection pitch	115 mm without spreader
Contact position indicator	Yes
[Icm] rated short-circuit making capacity	143 KA (Icm) at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 105 kA (Icm) at 690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	65 KA (1 s) at 220...440 V AC 50/60 Hz conforming to IEC 60947-2 50 KA (1 s) at 690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA (3 s) at 440/690 V AC 50/60 Hz conforming to IEC 60947-2
Trip unit protection functions	LSI

Protection type	Instantaneous short-circuit protection Overload protection (long time) Short time short-circuit protection
Long time pick-up adjustment type I_r	Adjustable 9 settings
Long time pick-up adjustment range	0.4...1 x I_n
Long time delay adjustment type	Adjustable 9 settings
$[t_r]$ long-time delay adjustment range	0.5...24 s at 6 x I_r
Thermal memory	20 minutes before and after tripping
Short-time pick-up adjustment type I_{sd}	Adjustable 9 settings
$[I_{sd}]$ short-time pick-up adjustment range	1.5...10 x I_r
Short-time delay adjustment type	Adjustable 5 settings
$[t_{sd}]$ short-time delay adjustment range	100...400 ms
Instantaneous pick-up adjustment type I_i	Adjustable 9 settings
Instantaneous pick-up adjustment range	2...15 x I_n Off
Zone selective interlocking ZSI	With
Maximum breaking time	25 ms
Maximum closing response time	70 ms
Height	439 mm
Width	556 mm
Depth	395 mm
Net weight	90 kg

Environment

Standards	IEC 60947-2
Product certifications	IEC[RETURN]EAC
Pollution degree	4 conforming to IEC 60664-1
IP degree of protection	IP40
Ambient air temperature for operation	-5...70 °C
Ambient air temperature for storage	-40...85 °C without control unit -25...85 °C with control unit

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	43.9 cm
Package 1 Width	55.6 cm
Package 1 Length	39.5 cm
Package 1 Weight	120 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
PVC free	Yes