



## Main

Product line	QO
Product type	Bar



## Complementary

Number of connectors	15
Wire size	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium
Provided equipment	2 screw
Bar length	143 mm
Maximum length of segment	80 mm
Device mounting	Direct mounting back of enclosure
Height	11.10 Mm 11.10 mm
Depth	7.92 Mm 7.92 mm
Tightening torque	: 30 lb.in Mounting screw: 30 lb.in : 20 lb.in, AWG 14...AWG 10, copper : 20 lb.in, AWG 12...AWG 10, aluminium : 25 lb.in, AWG 8 : 35 lb.in, AWG 6...AWG 4 : 25 lb.in, AWG 14...AWG 12, copper : 25 lb.in, AWG 12...AWG 10, aluminium

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.032 cm
Package 1 Width	1.27 cm
Package 1 Length	14.478 cm
Package 1 Weight	68.039 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.906 cm
Package 2 Width	16.002 cm
Package 2 Length	18.542 cm
Package 2 Weight	775.643 g
Unit Type of Package 3	PAL
Number of Units in Package 3	2160
Package 3 Height	71.12 cm

Package 3 Width	101.6 cm
Package 3 Length	121.92 cm
Package 3 Weight	186.426 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------