

### Main

|                           |  |
|---------------------------|--|
| Range of product          | Modicon M221   |
| Product or component type | Logic controller   |
| [Us] rated supply voltage | 24 V DC  |
| Discrete input number     | 24, discrete input 4 fast input conforming to IEC 61131-2 Type 1 |
| Analogue input number     | 2 at 0...10 V  |
| Discrete output type      | Transistor   |
| Discrete output number    | 16 transistor 2 fast output                                      |
| Discrete output voltage   | 24 V DC  |
| Discrete output current   | 0.5 A  |

### Complementary

|  |   |
|--|---|
| Discrete I/O number                    | 40  |
| Maximum number of I/O expansion module | 7 (local I/O-Architecture)<br>14 (remote I/O-Architecture)  |
| Supply voltage limits                  | 20.4...28.8 V   |
| Inrush current                         | 35 A  |
| Maximum power consumption in W         | 17 W at 24 V (with max number of I/O expansion module)<br>4.9 W at 24 V (without I/O expansion module)  |
| Power supply output current            | 0.52 A 5 V for expansion bus<br>0.3 A 24 V for expansion bus  |
| Discrete input logic                   | Sink or source (positive/negative)  |
| Discrete input voltage                 | 24 V  |
| Discrete input voltage type            | DC  |
| Analogue input resolution              | 10 bits   |
| LSB value                              | 10 mV   |
| Conversion time                        | 1 ms per channel + 1 controller cycle time for analogue input analog input  |
| Permitted overload on inputs           | +/- 30 V DC for 5 min (maximum) for analog input<br>+/- 13 V DC (permanent) for analog input  |
| Voltage state 1 guaranteed             | >= 15 V for input   |
| Voltage state 0 guaranteed             | <= 5 V for input  |
| Discrete input current                 | 7 mA for discrete input<br>5 mA for fast input  |
| Input impedance                        | 3.4 kOhm for discrete input<br>100 kOhm for analog input<br>4.9 kOhm for fast input   |
| Response time                          | 35 µs turn-off, I2...I5 terminal(s) for input<br>5 µs turn-on, I0, I1, I6, I7 terminal(s) for fast input<br>35 µs turn-on, other terminals terminal(s) for input<br>5 µs turn-off, I0, I1, I6, I7 terminal(s) for fast input<br>100 µs turn-off, other terminals terminal(s) for input<br>5 µs turn-on, turn-off, Q0...Q1 terminal(s) for output<br>50 µs turn-on, turn-off, Q2...Q3 terminal(s) for output<br>300 µs turn-on, turn-off, other terminals terminal(s) for output |
| Configurable filtering time            | 0 ms for input<br>3 ms for input<br>12 ms for input   |
| Discrete output logic                  | Positive logic (source)   |
| Maximum current per output common      | 4 A   |
| Output frequency                       | 100 KHz for fast output (PWM/PLS mode) at Q0...Q1<br>5 KHz for output at Q2...Q3<br>0.1 kHz for output at Q4...Q15  |

|                                   |   |
|-----------------------------------|---|
| Absolute accuracy error           | +/- 1 % of full scale for analog input  |
| Maximum leakage current           | 0.1 mA for transistor output  |
| Maximum voltage drop              | <1 V  |
| Mechanical durability             | 20000000 cycles for transistor output   |
| Maximum tungsten load             | <12 W for output and fast output  |
| Protection type                   | Overload and short-circuit protection at 1 A  |
| Reset time                        | 1 s automatic reset   |
| Memory capacity                   | 256 kB for user application and data RAM with 10000 instructions<br>256 kB for internal variables RAM   |
| Data backed up                    | 256 kB built-in flash memory for backup of application and data   |
| Data storage equipment            | 2 GB SD card (optional)   |
| Battery type                      | BR2032 or CR2032X lithium non-rechargeable  |
| Backup time                       | 1 year at 25 °C (by interruption of power supply)   |
| Execution time for 1 KInstruction | 0.3 ms for event and periodic task  |
| Execution time per instruction    | 0.2 µs Boolean  |
| Exct time for event task          | 60 µs response time   |
| Maximum size of object areas      | 512 %KW constant words<br>255 %TM timers<br>255 %C counters<br>8000 %MW memory words<br>512 %M memory bits  |
| Realtime clock                    | With  |
| Clock drift                       | <= 30 s/month at 25 °C  |
| Regulation loop                   | Adjustable PID regulator up to 14 simultaneous loops  |
| Positioning functions             | Position PTO 2 axe(s)pulse/direction mode (100 kHz)<br>Position PTO 1 axe(s)CW/CCW mode (100 kHz)   |
| Function available                | PWM<br>PLS<br>Frequency generator   |
| Counting input number             | 4 fast input (HSC mode) at 100 kHz 32 bits  |
| Counter function                  | A/B<br>Pulse/Direction<br>Single phase  |
| Integrated connection type        | USB port with mini B USB 2.0 connector<br>Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface<br>Ethernet with RJ45 connector   |
| Supply                            | (serial)serial link supply: 5 V, <200 mA  |
| Transmission rate                 | 1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485<br>1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232<br>480 Mbit/s for USB   |
| Communication port protocol       | USB port: USB - SoMachine-Network<br>Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network<br>Ethernet   |
| Port Ethernet                     | 10BASE-T/100BASE-TX 1 port with 100 m copper cable  |
| Communication service             | Modbus TCP slave device<br>Ethernet/IP adapter<br>Modbus TCP server<br>Modbus TCP client<br>DHCP client   |
| Local signalling                  | 1 LED (green) for PWR<br>1 LED (green) for RUN<br>1 LED (red) for module error (ERR)<br>1 LED (green) for SD card access (SD)<br>1 LED (red) for BAT<br>1 LED per channel (green) for I/O state<br>1 LED (green) for SL<br>Ethernet network activity (green) for ACT<br>Ethernet network link (yellow) for Link (Link Status) |
| Electrical connection             | Removable screw terminal block for inputs<br>Removable screw terminal block for outputs<br>Terminal block, 3 terminal(s) for connecting the 24 V DC power supply<br>Connector, 4 terminal(s) for analogue inputs<br>Mini B USB 2.0 connector for a programming terminal   |

|  |  |
|--|--|
| Maximum cable distance between devices | Shielded cable: <10 m for fast input<br>Unshielded cable: <30 m for output<br>Unshielded cable: <30 m for digital input<br>Unshielded cable: <1 m for analog input<br>Shielded cable: <3 m for fast output   |
| Insulation                             | Between input and internal logic at 500 V AC<br>Between fast input and internal logic at 500 V AC<br>Non-insulated between inputs<br>Between output and internal logic at 500 V AC<br>Non-insulated between analogue input and internal logic<br>Non-insulated between analogue inputs |
| Marking                                | CE   |
| Mounting support                       | Top hat type TH35-15 rail conforming to IEC 60715<br>Top hat type TH35-7.5 rail conforming to IEC 60715<br>Plate or panel with fixing kit  |
| Height                                 | 90 mm  |
| Depth                                  | 70 mm  |
| Width                                  | 160 mm   |
| Net weight                             | 0.456 kg   |

## Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | IEC 61131-2<br>UL 508<br>CAN/CSA C22.2 No. 213<br>IACS E10<br>ANSI/ISA 12-12-01   |
| Product certifications                | RCM[RETURN]EAC[RETURN]ABS[RETURN]LR[RETURN]cULus[RETURN]DNV-GL[RETURN]CE[RETURN]UKCA[RETURN]cULus HazLoc  |
| Environmental characteristic          | Ordinary and hazardous location   |
| Resistance to electrostatic discharge | 8 kV in air conforming to IEC 61000-4-2<br>4 kV on contact conforming to IEC 61000-4-2  |
| Resistance to electromagnetic fields  | 10 V/M 80 MHz...1 GHz conforming to IEC 61000-4-3<br>3 V/M 1.4 GHz...2 GHz conforming to IEC 61000-4-3<br>1 V/m 2...2.7 GHz conforming to IEC 61000-4-3   |
| Resistance to magnetic fields         | 30 A/m 50/60 Hz conforming to IEC 61000-4-8   |
| Resistance to fast transients         | 2 kV (power lines) conforming to IEC 61000-4-4<br>2 kV (relay output) conforming to IEC 61000-4-4<br>1 kV (I/O) conforming to IEC 61000-4-4<br>1 kV (Ethernet line) conforming to IEC 61000-4-4<br>1 kV (serial link) conforming to IEC 61000-4-4   |
| Surge withstand                       | 2 kV power lines (AC) common mode conforming to IEC 61000-4-5<br>2 kV relay output common mode conforming to IEC 61000-4-5<br>1 kV I/O common mode conforming to IEC 61000-4-5<br>1 kV shielded cable common mode conforming to IEC 61000-4-5<br>0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5<br>1 kV power lines (AC) differential mode conforming to IEC 61000-4-5<br>1 kV relay output differential mode conforming to IEC 61000-4-5<br>0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5   |
| Resistance to conducted disturbances  | 10 V 0.15...80 MHz conforming to IEC 61000-4-6<br>3 V 0.1...80 MHz conforming to Marine specification (LR, ABS, DNV, GL)<br>10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)   |
| Electromagnetic emission              | Conducted emissions - test level: 79 dB $\mu$ V/m QP/66 dB $\mu$ V/m AV ( power lines (AC)) at 0.15...0.5 MHz conforming to IEC 55011<br>Conducted emissions - test level: 73 dB $\mu$ V/m QP/60 dB $\mu$ V/m AV ( power lines (AC)) at 0.5...300 MHz conforming to IEC 55011<br>Conducted emissions - test level: 120...69 dB $\mu$ V/m QP ( power lines) at 10...150 kHz conforming to IEC 55011<br>Conducted emissions - test level: 63 dB $\mu$ V/m QP ( power lines) at 1.5...30 MHz conforming to IEC 55011<br>Radiated emissions - test level: 40 dB $\mu$ V/m QP class A ( 10 m) at 30...230 MHz conforming to IEC 55011<br>Conducted emissions - test level: 79...63 dB $\mu$ V/m QP ( power lines) at 150...1500 kHz conforming to IEC 55011<br>Radiated emissions - test level: 47 dB $\mu$ V/m QP class A ( 10 m) at 200...1000 MHz conforming to IEC 55011 |
| Immunity to microbreaks               | 10 ms   |
| Ambient air temperature for operation | -10...55 °C (horizontal installation)<br>-10...35 °C (vertical installation)  |
| Ambient air temperature for storage   | -25...70 °C   |

|                         |  |
|-------------------------|--|
| Relative humidity       | 10...95 %, without condensation (in operation)<br>10...95 %, without condensation (in storage)   |
| IP degree of protection | IP20 with protective cover in place  |
| Pollution degree        | <= 2   |
| Operating altitude      | 0...2000 m   |
| Storage altitude        | 0...3000 m   |
| Vibration resistance    | 3.5 mm at 5...8.4 Hz on symmetrical rail<br>3.5 mm at 5...8.4 Hz on panel mounting<br>1 gn at 8.4...150 Hz on symmetrical rail<br>1 gn at 8.4...150 Hz on panel mounting |
| Shock resistance        | 147 m/s <sup>2</sup> for 11 ms   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 11.139 cm |
| Package 1 Width              | 14.201 cm |
| Package 1 Length             | 21.045 cm |
| Package 1 Weight             | 760.0 g   |
| Unit Type of Package 2       | CAR       |
| Number of Units in Package 2 | 12        |
| Package 2 Height             | 29.3 cm   |
| Package 2 Width              | 39.2 cm   |
| Package 2 Length             | 56.9 cm   |
| Package 2 Weight             | 10.211 kg |
| Unit Type of Package 3       | P12       |
| Number of Units in Package 3 | 144       |
| Package 3 Height             | 105.0 cm  |
| Package 3 Width              | 120.0 cm  |
| Package 3 Length             | 80.0 cm   |
| Package 3 Weight             | 132 kg    |

## Offer Sustainability

|   |   |
|---|---|
| SCIP Number   | 7ae73ccc-0a66-472c-8f06-8951f8377fa6  |
| Packaging without single use plastic                  | Yes   |
| Packaging made with recycled cardboard                | No  |
| REACH Regulation                                      | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive                                     | Pro-active compliance (Product out of EU RoHS legal scope)  |
| Mercury free  | Yes   |
| China RoHS Regulation                                 | <a href="#">China RoHS Declaration</a>  |
| RoHS exemption information                            | <a href="#">Yes</a>   |
| Environmental Disclosure                              | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile                                   | <a href="#">End Of Life Information</a>   |
| WEEE  | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| PVC free  | Yes   |
| Take-back   | No  |
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 128   |