



Main

Range	AvatarOn
Product or component type	Power strip
Shape	Rectangular
Control type	Switch
Socket number	6
Integrated connection type	6 USB port 250 V AC, maximum load current: 13 A
Cable length	3 m

Complementary

Number of socket outlets with earth pin	6
[Ue] rated operational voltage	250 V
Number of USB connection	2
[In] rated current	13 A
On/off switch present	True
Outlet standard deviation	BS 1363
Surge protection present	False
Marking	Without symbol
Cover present	False
Socket additional information	Shuttered
Pilot light	ON indicator
Material	PC (polycarbonate)
Length	400.5 mm
Width	61 mm
Depth	32 mm
Type of packing	Blister
Cable cross section	0...1.25 mm ²
Colour	Metal gold hairline
Surface treatment	Untreated
Height	32 mm
Net weight	0.742 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8.0 cm
Package 1 Length	46.0 cm
Package 1 Weight	886.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm

Package 2 Length	60.0 cm
Package 2 Weight	11.392 kg
Unit Type of Package 3	P12
Number of Units in Package 3	144
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	148.704 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information