



## Main

Range	ComPact
Range of product	ComPacT NSXm new generation
Device short name	MN
Product or component type	Voltage release
Device application	Control
Voltage release type	Opening coil Undervoltage release
[Uc] control circuit voltage	220...240 V AC 50 Hz 208...240 V AC 60 Hz
Range compatibility	ComPact ComPacT NSXm new generation ComPact ComPact NSXm PowerPact PowerPact B

## Complementary

Operating threshold	0.35...0.7 x Un opening 0.85 x Un closing
Response time	< 50 ms
Auxiliary connection terminal	Pre-wired 0...0.8 mm <sup>2</sup> (AWG 18)stranded copper
Wire stripping length	8 mm
Cable length	1 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6 cm
Package 1 Length	8.5 cm
Package 1 Weight	83 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9 cm
Package 2 Width	13 cm
Package 2 Length	18.5 cm
Package 2 Weight	880 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	10.9 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	<a href="#"> End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins