

XVC4B45S

Complete pre wired monolithic tower light,
Harmony XVC, plastic, red orange green
blue, 40mm, tube mounting, steady or flashing,
buzzer, IP23, 24V AC DC



Main

| | |
|------------------------------------|--|
| Range of product | Harmony XVC4 |
| Product or component type | Complete pre-wired monolithic tower light |
| Beacon or indicator bank unit type | 4 illuminated units |
| Sound signalling | Buzzer |
| Mounting diameter | 40 mm |
| Component name | XVC |
| Device short name | XVC |
| Light source | LED steady or flashing red LED steady or flashing orange LED steady or flashing green LED steady or flashing blue |
| Supply circuit type | AC/DC |
| Noise level | 70...85 dB (continuous or intermittent tone) at 1 m |

Complementary

| | |
|--|---|
| Material | Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover SGP (chromium-plated): support tube |
| Mounting location | On support tube, 17 mm |
| Product mounting | On support tube, 17 mm |
| [Us] rated supply voltage | 24 V |
| [Us] rated supply voltage | 24 V |
| Cable cross section | 0.33 mm ² |
| AWG gauge | AWG 22 |
| Cable length | 900 mm |
| Marking | CE |
| [Uimp] rated impulse withstand voltage | 0.8 kV |
| Current consumption | 140 mA |
| Fundamental frequency | 2.23 kHz |
| Flashing frequency | 1 Hz |
| Net weight | 0.66 kg |
| Height | 629.5 mm |





Environment

| | |
|---------------------------------------|--|
| Standards | IEC 61000-6-3 IEC 61000-6-2 |
| Product certifications | UL |
| Protective treatment | TC |
| Ambient air temperature for storage | -35...70 °C |
| Ambient air temperature for operation | -10...50 °C |
| Electrical shock protection class | Class I conforming to IEC 61140 |
| Overvoltage category | Class I conforming to IEC 61140 |
| IP degree of protection | IP23 vertical surface installation conforming to IEC 60529 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 6.6 cm |
| Package 1 Width | 6.6 cm |
| Package 1 Length | 74.9 cm |
| Package 1 Weight | 880.0 g |
| Unit Type of Package 2 | P06 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 45.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 18.0 kg |

Offer Sustainability

| | |
|----------------------------|---|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile |  End Of Life Information |


Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b1 dimension.



| No. of illuminated units | b1 With buzzer (mm) | b1 With buzzer (in.) |
|--------------------------|---------------------|----------------------|
| 1 stage | 524.50 | 20.65 |
| 2 stages | 559.50 | 22.03 |
| 3 stages | 594.50 | 23.41 |
| 4 stages | 629.50 | 24.78 |
| 5 stages | 664.50 | 26.16 |

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting

