



### Main

Range	MasterPact
Device short name	Second MX
Product or component type	Voltage release
Device application	Control
Range compatibility	Masterpact (MasterPact MTZ1) circuit-breaker
Voltage release type	Shunt trip release

### Complementary

Control type	Standard
[Un] voltage power supply	100...130 V AC 50/60 Hz 100...130 V DC
Threshold tripping voltage	0.7...1.1 Un on opening
Holding power consumption	4.5 W
Circuit breaker mounting mode	Drawout
Maximum response time	60 ms on opening for MasterPact MTZ1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.3 cm
Package 1 Length	8.1 cm
Package 1 Weight	1.167 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.