



Main

Range	MasterPacT
Product name	MasterPact MTZ3
Device short name	MTZ3 63 H1
Product or component type	Circuit breaker
Device application	Power distribution protection
Poles description	4P
Neutral position	Left
Control unit	Without control unit
Product compatibility	Control unit MicroLogic 2.0 X Control unit MicroLogic 5.0 X Control unit MicroLogic 6.0 X Control unit MicroLogic 7.0 X Control unit MicroLogic 2.0 Xi Control unit MicroLogic 5.0 Xi Control unit MicroLogic 6.0 Xi Control unit MicroLogic 7.0 Xi
[In] rated current	6300 A at 40 °C
Performance type	H1 100 kA 415 V AC
[Ue] rated operational voltage	690 V AC 50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Selectivity category	Category B
Control type	Push-button
Mounting mode	Fixed

Complementary

[Icu] rated ultimate short-circuit breaking capacity	100 KA at 220/415 V AC 50/60 Hz 100 KA at 440 V AC 50/60 Hz 100 KA at 500/525 V AC 50/60 Hz 100 kA at 660/690 V AC 50/60 Hz
[Ics] rated service breaking capacity	100 KA at 220/415 V AC 50/60 Hz 100 KA at 440 V AC 50/60 Hz 100 KA at 500/525 V AC 50/60 Hz 100 kA at 660/690 V AC 50/60 Hz
[Icw] rated short-time withstand current	100 KA 0.5 s 100 KA 1 s 100 kA 3 s
[Icm] rated short-circuit making capacity	220 KA 220/415 V AC at 50/60 Hz 220 KA 440 V AC at 50/60 Hz 220 KA 500/525 V AC at 50/60 Hz 220 kA 660/690 V AC at 50/60 Hz
Sensor rating	3200 A 4000 A 5000 A 6300 A
[Ui] rated insulation voltage	1000 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	12 kV
Power dissipation in W	650 W
Maximum breaking time	25 ms
Maximum closing response time	80 ms
Mounting support	Rails Base plate

Upside connection	Rear
Downside connection	Rear
Connection pitch	230 mm
Mechanical durability	10000 cycles with periodic preventive maintenance
Electrical durability	AC-3: 6000 cycles 440/690 V AC 50/60 Hz conforming to EN/IEC 60947-3 1500 Cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 1500 Cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-23A: 1500 cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-23A: 1500 cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-3
Height	352 mm
Width	997 mm
Depth	300 mm
Net weight	160 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-2 Annex H IEC 61557-12
Product certifications	CE[RETURN]IECEE CB Scheme

Environment

IP degree of protection	IP30 conforming to EN 60529
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	0...2000 m without derating 2000...5000 m with derating

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	60.0 cm
Package 1 Width	50.0 cm
Package 1 Length	120.0 cm
Package 1 Weight	145.13 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
PVC free	Yes