



Main

Range	MasterPacT
Product name	MasterPact MTZ2
Device short name	MTZ2 16 H2
Product or component type	Circuit breaker
Device application	Power distribution protection
Poles description	3P
Control unit	Without control unit
Product compatibility	Control unit MicroLogic 2.0 X Control unit MicroLogic 5.0 X Control unit MicroLogic 6.0 X Control unit MicroLogic 7.0 X Control unit MicroLogic 2.0 Xi Control unit MicroLogic 5.0 Xi Control unit MicroLogic 6.0 Xi Control unit MicroLogic 7.0 Xi
[In] rated current	1600 A at 40 °C
Performance type	H2 100 kA 415 V AC
[Ue] rated operational voltage	690 V AC 50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Selectivity category	Category B
Control type	Push-button
Mounting mode	Drawout

Complementary

[Icu] rated ultimate short-circuit breaking capacity	100 KA at 220/415 V AC 50/60 Hz 100 KA at 440 V AC 50/60 Hz 85 KA at 500/525 V AC 50/60 Hz 85 KA at 660/690 V AC 50/60 Hz
[Ics] rated service breaking capacity	100 KA at 220/415 V AC 50/60 Hz 100 KA at 440 V AC 50/60 Hz 85 KA at 500/525 V AC 50/60 Hz 85 KA at 660/690 V AC 50/60 Hz
[Icw] rated short-time withstand current	85 KA 0.5 s 85 KA 1 s 50 kA 3 s
[Icm] rated short-circuit making capacity	220 KA 220/415 V AC at 50/60 Hz 220 KA 440 V AC at 50/60 Hz 187 KA 500/525 V AC at 50/60 Hz 187 KA 660/690 V AC at 50/60 Hz
Integrated instantaneous protection (DIN in kA peak)	171...209 kA
Sensor rating	800 A 1000 A 1250 A 1600 A
[Ui] rated insulation voltage	1000 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	12 kV
Power dissipation in W	390 W
Maximum breaking time	25 ms
Maximum closing response time	70 ms
Mounting support	Rails Base plate

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Upside connection	Front Rear
Downside connection	Front Rear
Connection pitch	115 mm
Mechanical durability	25000 cycles with periodic preventive maintenance
Electrical durability	10000 Cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10000 Cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-2 AC-23A: 10000 cycles 440 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-23A: 10000 cycles 690 V AC 50/60 Hz conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440/690 V AC 50/60 Hz conforming to EN/IEC 60947-3
Height	Drawout circuit breaker with chassis: 439 mm Drawout circuit breaker without chassis: 300 mm
Width	Drawout circuit breaker with chassis: 441 mm Drawout circuit breaker without chassis: 378 mm
Depth	Drawout circuit breaker with chassis: 403 mm Drawout circuit breaker without chassis: 300 mm
Net weight	90 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-2 Annex H IEC 61557-12
Product certifications	CE[RETURN]IECEE CB Scheme





Environment

IP degree of protection	IP30 conforming to EN 60529
Pollution degree	3 conforming to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	0...2000 m without derating 2000...5000 m with derating

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	29.5 cm
Package 1 Length	37.5 cm
Package 1 Weight	47.035 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
PVC free	Yes